

MASI67 I/O MODULE

4 digital inputs, 4 digital outputs

Digital inputs/outputs

DI4 - 1.6 A DO4 - 2 A - 4x M12

Double assignment of M12 females, PIN 2 + 4

Sensor supply from external 24 V DC

Connection cables are in the online shop under "Connection Technology".


Housing fully potted.

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
GTIN	4048879049078
Gümrük tarife no (gtip)	85176200
Paket miktarı	1

Electrical data | Supply

Norm operating voltage	EN 61131-2
Operating voltage UA DC	24 V
Operating voltage UA DC min.	18 V
Operating voltage UA DC max.	30,2 V
Bus voltage AS-Interface DC min.	26,5 V
Bus voltage AS-Interface DC max.	31,6 V

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.

Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmalî sınırlıdır. Sürüm: 2024-04-19

Murrelektronik GmbH | Falkenstr. 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Current consumption AS-i port max.	50 mA
------------------------------------	-------

Total current max.	8 A
--------------------	-----

Electrical data | Input

Overload resistant	yes
--------------------	-----

Short-circuit protected	yes
-------------------------	-----

Type input	PNP, for 3-wire sensors or mechanical switches
------------	--

Current carrying capacity max.	1,6 A
--------------------------------	-------

Electrical data | Output

Overload resistant	yes
--------------------	-----

Short-circuit protected	yes
-------------------------	-----

Output current per pin max.	2 A
-----------------------------	-----

Industrial communication | Bus data

Address setting type	Addressing socket, Master
----------------------	---------------------------

Slave address range	(0), 1 ...
---------------------	------------

Industrial communication | AS-Interface

Profile (IO.ID.ID2)	S-7.F.E
---------------------	---------

Diagnostics

Diagnostic	No voltage
------------	------------

Diagnostic via LED	per module
--------------------	------------

LED display	Ethernet connection/data traffic
-------------	----------------------------------

Installation | Connection

Double assignment M12 female	yes
------------------------------	-----

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Mounting method	screwed, geschnappt
-----------------	---------------------

Suitable for mounting type	mounting rail, (EN 60715)
----------------------------	---------------------------

Height	94 mm
--------	-------

Width	60 mm
-------	-------

Depth	39 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Storage temperature min.	-20 °C
--------------------------	--------

Storage temperature max.	70 °C
--------------------------	-------

Connection type 1

Connection type 1	0-3
-------------------	-----

Family construction form	M12
--------------------------	-----

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Coding	A
--------	---

No. of poles	5
--------------	---

PIN 1	Usens +
-------	---------

PIN 2	DI
-------	----

PIN 3	Usens -
-------	---------

PIN 4	DI
-------	----

PIN 5	n.c.
-------	------