


50M MAIN CABLE PUR/PVC-JB 4\*0,34+3\*0,75

4-way distribution boxes M12  
PUR/PVC  
4× 0.34 + 3× 0.75 mm²

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료                 |                                                       |
|----------------------|-------------------------------------------------------|
| ECLASS-6.0           | 27062011                                              |
| ECLASS-6.1           | 27279218                                              |
| ECLASS-7.0           | 27279218                                              |
| ECLASS-8.0           | 27279218                                              |
| ECLASS-9.0           | 27060311                                              |
| ECLASS-10.1          | 27061801                                              |
| ECLASS-11.1          | 27061801                                              |
| ECLASS-12.0          | 27061801                                              |
| ETIM-5.0             | EC001578                                              |
| GTIN                 | 4048879057325                                         |
| 세번부호                 | 85444995                                              |
| 포장단위                 | 1                                                     |
| Installation   Cable |                                                       |
| Cable identification | 333                                                   |
| Cable Type           | 2                                                     |
| Jacket Color         | gray                                                  |
| Type of Certificate  | cURus                                                 |
| STOOW style jacket   | Hybrid, Signal, Power                                 |
| Amount stranding     | 1                                                     |
| Stranding            | 7 wires around Core filler twisted                    |
| Filler               | yes                                                   |
| wire arrangement     | white, green, yellow, gray, brown, blue, green-yellow |
| Cable weighth        | 105,6 g/m                                             |

|                                                         |                                                      |
|---------------------------------------------------------|------------------------------------------------------|
| Material jacket                                         | PUR                                                  |
| Shore hardness jacket                                   | 87 ± 5 Shore A                                       |
| Freedom from ingredients (jacket)                       | lead-free, cadmium-free, CFC-free, silicone-free     |
| Outer-diameter (jacket)                                 | 7,4 mm                                               |
| Tolerance outer diameter (sheath)                       | ± 5 %                                                |
| Material inner jacket                                   | PVC                                                  |
| Color (inner jacket)                                    | gray                                                 |
| Material wire insulation                                | PVC                                                  |
| Amount wires                                            | 4                                                    |
| Outer diameter insulation                               | 1,3 mm                                               |
| Outer diameter tolerance core insulation                | ± 5 %                                                |
| Shore hardness wire insulation                          | 43 ± 5 Shore D                                       |
| Material properties wire insulation                     | good machinability                                   |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands (wire)                                   | 19                                                   |
| Diameter of single wires                                | 0,15 mm                                              |
| Conductor crosssection (wire)                           | 0,34 mm <sup>2</sup>                                 |
| Material conductor wire                                 | Stranded copper wire, bare                           |
| Conductor type (wire)                                   | Strand class 5                                       |
| Material wire insulation (Power)                        | PVC                                                  |
| Outer diameter wire insulation (Power)                  | 1,8 mm                                               |
| Tolerance outer diameter wire insulation (Power)        | ±5 %                                                 |
| Shore hardness wire insulation (Power)                  | 43±5 Shore D                                         |
| Material properties wire insulation (Power)             | good machinability                                   |
| Ingredient freeness wire insulation (Power)             | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount wires (Power)                                    | 3                                                    |
| Amount strands wire (Power)                             | 24                                                   |
| Diameter of single wires (Power)                        | 0,2 mm                                               |
| Wire conductor cross section (Power)                    | 0,75 mm <sup>2</sup>                                 |
| Material conductor wire (Power)                         | Stranded copper wire, bare                           |
| Conductor type wire (Power)                             | Strand class 5                                       |
| Traversing distance (C-track)                           | 5 m                                                  |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                         | 4 A                                                  |
| Electrical resistance line constant wire                | 57 Ω/km @ 20 °C                                      |
| Electrical resistance coating wire (Power)              | 26 Ω/km @20 °C                                       |
| Loop resistance                                         | 7,8 A                                                |
| Max. rated voltage power (conductor - ground)           | 300 V                                                |
| Max. rated voltage power (conductor - conductor)        | 300 V                                                |
| Power frequency withstand voltage power (wire - jacket) | 2 kV @ 60 s                                          |
| AC withstand voltage power (wire - wire)                | 2 kV @ 60 s                                          |
| Min. operating temperature (static)                     | -30 °C                                               |
| Max. operating temperature (fixed)                      | 80 °C                                                |
| Operating temperature min. (dynamic)                    | -5 °C                                                |
| Operating temperature max. (dynamic)                    | 70 °C                                                |
| Flame resistance                                        | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2  |
| chemical resistance                                     | Good, application-related testing                    |
| Gasoline resistance                                     | Good, application-related testing                    |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404 |
| No. of bending cycles (C-track)                         | 2 Mio.                                               |
| Bending radius (fixed)                                  | 5 x Outer diameter                                   |
| Bending radius (dynamic)                                | 10 x Outer diameter                                  |