

**MASI68 I/O EXTENSION MODULE**

4 analog Inputs U/I configurable


AI4 - (E) 4× M12 (UI)

Connection cables are in the online shop under "Connection Technology".


Housing fully potted.

**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27242601      |
| ECLASS-6.1              | 27242601      |
| ECLASS-7.0              | 27242601      |
| ECLASS-8.0              | 27242601      |
| ECLASS-9.0              | 27242601      |
| ECLASS-10.1             | 27242601      |
| ECLASS-11.1             | 27242601      |
| ECLASS-12.0             | 27242601      |
| ETIM-5.0                | EC001596      |
| GTIN                    | 4048879496681 |
| Gümrük tarife no (gtip) | 85176200      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                                    |            |
|------------------------------------|------------|
| Norm operating voltage             | EN 61131-2 |
| Operating voltage US DC            | 24 V       |
| Bus voltage AS-Interface DC min.   | 26,5 V     |
| Bus voltage AS-Interface DC max.   | 31,6 V     |
| Current consumption AS-i port max. | 100 mA     |

**Electrical data | Input**

|                         |     |
|-------------------------|-----|
| Overload resistant      | yes |
| Short-circuit protected | yes |

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.

Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmalı sınırlıdır. Sürüm: 2024-05-06

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Sensor current US per input max. 0,1 A

**Industrial communication | Bus data**

Address setting type M12 connection and programming device, Master  
Slave address range 1 ... 31

**Industrial communication | AS-Interface**

Profile (IO.ID.ID2) S-7.3.E

**Diagnostics**

Diagnostic No voltage  
Diagnostic via LED per module  
LED display Ethernet connection/data traffic

**Device protection | Electrical**

Degree of protection (EN IEC 60529) IP68

**Mechanical data | Mounting data**

Mounting method screwed  
Height 151 mm  
Width 30 mm  
Depth 34,5 mm

**Environmental characteristics | Climatic**

Operating temperature min. -20 °C  
Operating temperature max. 70 °C  
Storage temperature min. -40 °C  
Storage temperature max. 85 °C

**Connection type 3**

Connection type 1 0-3  
Connection type 2 Bus In  
Connection type 3 Bus Out  
Family construction form M12  
Gender female  
Color contact carrier black  
Coding A  
No. of poles 5  
PIN 1 24 V DC  
PIN 2 In +  
PIN 3 0 V  
PIN 4 In -  
PIN 5 n.c.  
Family construction form M12  
Gender male  
Color contact carrier black  
Coding A  
No. of poles 4  
PIN 1 AS-i +  
PIN 2 0 V  
PIN 3 AS-i -  
PIN 4 24 V DC  
Family construction form M12  
Gender female  
Color contact carrier black  
Coding A  
No. of poles 5  
PIN 1 AS-i +

|       |         |
|-------|---------|
| PIN 2 | 0 V     |
| PIN 3 | AS-i -  |
| PIN 4 | 24 V DC |
| PIN 5 | n.c.    |