

**CUBE20S POTENTIAL DISTRIBUTORS**

8 x 0 V DC


Potential distributor  
Expansion module  
8x 0 V DC

**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27379201      |
| ECLASS-6.1              | 27242611      |
| ECLASS-7.0              | 27242611      |
| ECLASS-8.0              | 27242611      |
| ECLASS-9.0              | 27242611      |
| ECLASS-10.1             | 27242611      |
| ECLASS-11.1             | 27242611      |
| ECLASS-12.0             | 27242611      |
| ETIM-5.0                | EC001600      |
| GTIN                    | 4048879422864 |
| Gümrük tarife no (gtip) | 85369010      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                           |      |
|---------------------------|------|
| Operating voltage DC max. | 0 V  |
| Total current max.        | 10 A |

**Device protection | Electrical**

|                                     |      |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP20 |
|-------------------------------------|------|

**Mechanical data | Mounting data**

|                            |                           |
|----------------------------|---------------------------|
| Mounting method            | geschnappt                |
| Suitable for mounting type | mounting rail, (EN 60715) |
| Height                     | 109 mm                    |

|                                                 |                           |
|-------------------------------------------------|---------------------------|
| Width                                           | 12,9 mm                   |
| Depth                                           | 52,5 mm                   |
| <b>Environmental characteristics   Climatic</b> |                           |
| Operating temperature min.                      | 0 °C                      |
| Operating temperature max.                      | 60 °C                     |
| Storage temperature min.                        | -25 °C                    |
| Storage temperature max.                        | 70 °C                     |
| <b>Connection type 2</b>                        |                           |
| Connection type 1                               | Power                     |
| Connection type 2                               | Power                     |
| Connection                                      | Spring clamp terminals FK |
| Family construction form                        | terminal                  |
| Gender                                          | female                    |
| No. of poles                                    | 8                         |
| PIN 1                                           | n.c.                      |
| PIN 2                                           | 24 V DC                   |
| PIN 3                                           | 0 V                       |
| PIN 4                                           | 24 V DC Sys               |
| PIN 5                                           | n.c.                      |
| PIN 6                                           | 24 V DC                   |
| PIN 7                                           | 0 V                       |
| PIN 8                                           | 0 V Sys                   |
| Connection                                      | Spring clamp terminals FK |
| Family construction form                        | terminal                  |
| Gender                                          | female                    |
| No. of poles                                    | 8                         |
| PIN 1                                           | 0 V DC                    |
| PIN 2                                           | 0 V DC                    |
| PIN 3                                           | 0 V DC                    |
| PIN 4                                           | 0 V DC                    |
| PIN 5                                           | 0 V DC                    |
| PIN 6                                           | 0 V DC                    |
| PIN 7                                           | 0 V DC                    |
| PIN 8                                           | 0 V DC                    |