

CUBE20S COUNTER MODULE

2X32Bit 400Khz 45 Parameter Bytes

Counter module


2× 32 Bit

max. 400 kHz

OUTPUT: 12 Byte

Ürün Linki**örnekleme**

Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27242605
ECLASS-6.1	27242605
ECLASS-7.0	27242605
ECLASS-8.0	27242605
ECLASS-9.0	27242605
ECLASS-10.1	27242605
ECLASS-11.1	27242605
ECLASS-12.0	27242605
ETIM-5.0	EC001601
GTIN	4048879422956
Gümrük tarife no (gtip)	90291000
Paket miktarı	1

Electrical data

Number of counters	2
Counter width	32 Bits
Counter frequency max.	400 kHz

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	20,4 V
Operating voltage DC max.	28,8 V

Current consumption max. 75 mA

Diagnostics

Diagnostic	Under voltage
Diagnostic via BUS	per module
Diagnostic via LED	per module
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

Device protection | Electrical

Degree of protection (EN IEC 60529) IP20

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	109 mm
Width	12,9 mm
Depth	76,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	70 °C

Connection type 2

Connection type 1	Power
Connection type 2	Power
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	A 0
PIN 2	24 V DC
PIN 3	0 V
PIN 4	A 1
PIN 5	B 0
PIN 6	24 V DC
PIN 7	0 V
PIN 8	B 1