



EXACT12, 4XM12, 5-POLE, MOULDED CABLE

3.0m PUR/PVC 8x0,34+3X0.75, UL/CSA


4-way, 5-pole  
PUR/PVC  
Further cable lengths on request.  
3.0 m  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료       |          |
|------------|----------|
| ECLASS-6.0 | 27279219 |
| ECLASS-6.1 | 27279219 |
| ECLASS-7.0 | 27279219 |
| ECLASS-8.0 | 27279219 |

|                                          |                                                                                                        |
|------------------------------------------|--------------------------------------------------------------------------------------------------------|
| ECLASS-9.0                               | 27440108                                                                                               |
| ECLASS-10.1                              | 27440108                                                                                               |
| ECLASS-11.1                              | 27440108                                                                                               |
| ECLASS-12.0                              | 27440108                                                                                               |
| ETIM-5.0                                 | EC002585                                                                                               |
| GTIN                                     | 4048879055826                                                                                          |
| 세번부호                                     | 85444290                                                                                               |
| 포장단위                                     | 1                                                                                                      |
| Electrical data   Supply                 |                                                                                                        |
| Operating voltage DC                     | 24 V                                                                                                   |
| Current operating per contact max.       | 4 A                                                                                                    |
| Installation   Connection                |                                                                                                        |
| Mounting set                             | M12 x 1                                                                                                |
| Device protection   Electrical           |                                                                                                        |
| Degree of protection (EN IEC 60529)      | IP65, IP67                                                                                             |
| Device protection   Media                |                                                                                                        |
| Flame resistance                         | flame retardant                                                                                        |
| Mechanical data   Material data          |                                                                                                        |
| Material housing                         | Plastic                                                                                                |
| Mechanical data   Mounting data          |                                                                                                        |
| Mounting method                          | Schraubgewinde                                                                                         |
| Environmental characteristics   Climatic |                                                                                                        |
| Operating temperature min.               | -20 °C                                                                                                 |
| Operating temperature max.               | 70 °C                                                                                                  |
| Additional condition temperature range   | depending on cable quality                                                                             |
| Installation   Cable                     |                                                                                                        |
| Cable identification                     | 363                                                                                                    |
| Cable Type                               | 2                                                                                                      |
| Jacket Color                             | gray                                                                                                   |
| Type of Certificate                      | cURus                                                                                                  |
| STOOW style jacket                       | Hybrid, Signal, Power                                                                                  |
| Amount stranding                         | 1                                                                                                      |
| Stranding                                | 2 wires with Filler twisted                                                                            |
| Amount stranding (type 2)                | 1                                                                                                      |
| Stranding (type 2)                       | 9 wires around Stranding combination twisted                                                           |
| Cable shielding (type)                   | copper braiding, bare                                                                                  |
| Cable shielding (coverage)               | 85 %                                                                                                   |
| Filler                                   | yes                                                                                                    |
| wire arrangement                         | white, yellow, (gray, gray-pink, red-blue, green, green-white, brown-green, blue, brown, green-yellow) |
| No. of bending cycles (C-track)          | 2 Mio. @ 25 °C                                                                                         |
| Cable weigth                             | 143 g/m                                                                                                |
| Material jacket                          | PUR                                                                                                    |
| Shore hardness jacket                    | 87 ± 5 Shore A                                                                                         |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, silicone-free                                                       |
| Outer-diameter (jacket)                  | 8,1 mm                                                                                                 |
| Tolerance outer diameter (sheath)        | ± 5 %                                                                                                  |
| Material inner jacket                    | PVC                                                                                                    |
| Color (inner jacket)                     | gray                                                                                                   |
| Material wire insulation                 | PVC                                                                                                    |
| Amount wires                             | 8                                                                                                      |
| Outer diameter insulation                | 1,3 mm                                                                                                 |

|                                                         |                                                      |
|---------------------------------------------------------|------------------------------------------------------|
| Outer diameter tolerance core insulation                | ± 5 %                                                |
| Shore hardness wire insulation                          | 43 ± 5 Shore D                                       |
| Material properties wire insulation                     | good machinability                                   |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands (wire)                                   | 19                                                   |
| Diameter of single wires                                | 0,15 mm                                              |
| Conductor crosssection (wire)                           | 0,34 mm²                                             |
| Material conductor wire                                 | Stranded copper wire, bare                           |
| Conductor type (wire)                                   | Strand class 5                                       |
| Material wire insulation (Power)                        | PVC                                                  |
| Outer diameter wire insulation (Power)                  | 1,8 mm                                               |
| Tolerance outer diameter wire insulation (Power)        | ±5 %                                                 |
| Shore hardness wire insulation (Power)                  | 43±5 Shore D                                         |
| Material properties wire insulation (Power)             | good machinability                                   |
| Ingredient freeness wire insulation (Power)             | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount wires (Power)                                    | 3                                                    |
| Amount strands wire (Power)                             | 24                                                   |
| Diameter of single wires (Power)                        | 0,2 mm                                               |
| Wire conductor cross section (Power)                    | 0,75 mm²                                             |
| Material conductor wire (Power)                         | Stranded copper wire, bare                           |
| Conductor type wire (Power)                             | Strand class 5                                       |
| Traversing distance (C-track)                           | 5 m @ 25 °C                                          |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                         | 4 A                                                  |
| Electrical resistance line constant wire                | 57 Ω/km @ 20 °C                                      |
| Electrical resistance coating wire (Power)              | 26 Ω/km @20 °C                                       |
| Loop resistance                                         | 7,8 A                                                |
| Max. rated voltage power (conductor - ground)           | 300 V                                                |
| Max. rated voltage power (conductor - conductor)        | 300 V                                                |
| Power frequency withstand voltage power (wire - jacket) | 2 kV @ 60 s                                          |
| AC withstand voltage power (wire - wire)                | 2 kV @ 60 s                                          |
| Min. operating temperature (static)                     | -30 °C                                               |
| Max. operating temperature (fixed)                      | 80 °C                                                |
| Operating temperature min. (dynamic)                    | -5 °C                                                |
| Operating temperature max. (dynamic)                    | 70 °C                                                |
| Flame resistance                                        | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090  |
| chemical resistance                                     | Good, application-related testing                    |
| Gasoline resistance                                     | Good, application-related testing                    |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                                  | 5 x Outer diameter                                   |
| Bending radius (dynamic)                                | 10 x Outer diameter                                  |

#### Connection type 2

|                          |                |
|--------------------------|----------------|
| Family construction form | free cable end |
| No. of poles             | 11             |
| Family construction form | M12            |
| Gender                   | female         |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 5              |
| PIN 1                    | +              |
| PIN 2                    | NC S 2         |
| PIN 3                    | -              |

|       |        |
|-------|--------|
| PIN 4 | NO S 1 |
| PIN 5 | PE     |