

## MB CAP ULTRA BUFFER MODULE

IN: 12/24VDC OUT:12/24VDC/10A for max.1A/380S



INPUT: 24 V DC (SELV/PELV)

OUTPUT: max. 10 A

38 s (10 A); 380 s (1 A)

### Ürün Linki

örnekleme



Ürün Image farklı olabilir



### Ticari bilgiler

|             |          |
|-------------|----------|
| ECLASS-6.0  | 27049190 |
| ECLASS-6.1  | 27049002 |
| ECLASS-7.0  | 27049002 |
| ECLASS-8.0  | 27049002 |
| ECLASS-9.0  | 27040705 |
| ECLASS-10.1 | 27040705 |

|                                                 |                                          |
|-------------------------------------------------|------------------------------------------|
| ECLASS-11.1                                     | 27040705                                 |
| ECLASS-12.0                                     | 27040705                                 |
| ETIM-5.0                                        | EC002584                                 |
| GTIN                                            | 4048879079785                            |
| Gümrük tarife no (gtip)                         | 85322900                                 |
| Paket miktarı                                   | 1                                        |
| <b>Electrical data</b>                          |                                          |
| Security level                                  | SELV/PELV                                |
| <b>Electrical data   Input</b>                  |                                          |
| Max. inrush current duration                    | 2 ms                                     |
| Input voltage 1 DC                              | 12 V                                     |
| Input voltage 1 DC min.                         | 11,9 V                                   |
| Input voltage 1 DC max.                         | 15 V                                     |
| Input voltage 2 DC                              | 24 V                                     |
| Input voltage 2 DC min.                         | 23,9 V                                   |
| Current input AC                                | 10 A                                     |
| Max. inrush current                             | 35 A                                     |
| Charging time min.                              | 100 s                                    |
| Charging time max.                              | 210 s                                    |
| Switching input potential free                  | 27 V                                     |
| Efficiency                                      | 90 %                                     |
| <b>Electrical data   Output</b>                 |                                          |
| Output voltage 1 DC                             | 11,3 V                                   |
| Output voltage 2 DC                             | 23,3 V                                   |
| Output voltage adjustable                       | yes                                      |
| Output current max.                             | 10 A                                     |
| <b>Mechanical data   Mounting data</b>          |                                          |
| Mounting method                                 | geschnappt                               |
| Suitable for mounting type                      | Tragschiene TH35-7.5/TH35-15, (EN 60715) |
| <b>Environmental characteristics   Climatic</b> |                                          |
| Operating temperature min.                      | -20 °C                                   |
| Operating temperature max.                      | 60 °C                                    |
| Storage temperature min.                        | -20 °C                                   |
| Storage temperature max.                        | 60 °C                                    |
| <b>Conformity</b>                               |                                          |
| Product standard                                | EN 60950, EN 50178                       |