

MPL POWER SUPPLY 3-PHASE, SMOOTHED

IN: 208-520VAC+/- 5% OUT: 24V/15ADC

Current: 15 A



Output rating: 360 W

This power supply units meet the (EN 61000-3-2) standard for harmonic current.

Any mounting position on vertical wall, condensation not permissible

Ürün Linki

örnekleme



Ürün Image farklı olabilir

Ticari bilgiler

ECLASS-6.0	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ETIM-5.0	EC002540
GTIN	4048879079112
Gümrük tarife no (gtip)	85044095
Paket miktarı	1

Electrical data

Security level	SELV
----------------	------

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.

Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmalı sınırlıdır. Sürüm: 2024-05-09

Murrelektronik GmbH | Falkenstr. 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage AC min.	208 V
-----------------------	-------

Input voltage AC max.	520 V
-----------------------	-------

Phase number input	3
--------------------	---

Efficiency	75 %
------------	------

Electrical data | Output

Fuse protection secondary side external	15 A
---	------

Output suppression	LED, Screening capacitor, VDR
--------------------	-------------------------------

Output voltage DC	24 V
-------------------	------

Output voltage adjustable	no
---------------------------	----

Output current max.	15 A
---------------------	------

Characteristic secondary fuse	Inertia
-------------------------------	---------

Ripple max.	2 %
-------------	-----

Mechanical data | Mounting data

Suitable for mounting type	Schlüssellochauhängung
----------------------------	------------------------

Mounting dimension a	195 mm
----------------------	--------

Mounting dimension b	59 mm
----------------------	-------

Mounting dimension c	6,5 mm
----------------------	--------

Height	220 mm
--------	--------

Width	81 mm
-------	-------

Depth	208 mm
-------	--------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	55 °C
----------------------------	-------

Conformity

Product standard	EN 61558-2-6, EN 62041 category I
------------------	-----------------------------------

EMC	EN 55011 B, EN 61000-3-2
-----	--------------------------