

## EXACT12, 4XM12, 5-POLE, CAP, PLUG. SCREW-TERM

W.o. LEDs

4-way, 5-pole

without LED, up to 125 V AC/DC

Screw plug-in terminals




Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

### 제품 링크

#### 일러스트



실제 제품은 이미지와 다를 수 있습니다.



#### 제품자료

|            |          |
|------------|----------|
| ECLASS-6.0 | 27279219 |
| ECLASS-6.1 | 27279219 |
| ECLASS-7.0 | 27279219 |

|             |               |
|-------------|---------------|
| ECLASS-8.0  | 27279219      |
| ECLASS-9.0  | 27440108      |
| ECLASS-10.1 | 27440111      |
| ECLASS-11.1 | 27440111      |
| ECLASS-12.0 | 27440111      |
| ETIM-5.0    | EC002585      |
| GTIN        | 4048879055611 |
| 세번부호        | 85369010      |
| 포장단위        | 1             |

Electrical data | Supply

|                                    |       |
|------------------------------------|-------|
| Operating voltage AC               | 125 V |
| Operating voltage DC               | 125 V |
| Current operating per contact max. | 4 A   |
| Total current max.                 | 8 A   |

Installation

|                               |                     |
|-------------------------------|---------------------|
| Connection cross section max. | 1,5 mm <sup>2</sup> |
| AWG number max.               | 16                  |

Installation | Connection

|            |                         |
|------------|-------------------------|
| Connection | Screw plug-in terminals |
|------------|-------------------------|

Device protection | Electrical

|                                     |            |
|-------------------------------------|------------|
| Degree of protection (EN IEC 60529) | IP65, IP67 |
|-------------------------------------|------------|

Device protection | Media

|                  |                 |
|------------------|-----------------|
| Flame resistance | flame retardant |
|------------------|-----------------|

Mechanical data | Material data

|                  |         |
|------------------|---------|
| Material housing | Plastic |
|------------------|---------|

Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
| Operating temperature max. | 70 °C  |

Connection type 2

|                          |        |
|--------------------------|--------|
| Family construction form | Cap    |
| No. of poles             | 16     |
| Family construction form | M12    |
| Gender                   | female |
| Color contact carrier    | black  |
| Coding                   | A      |
| No. of poles             | 5      |
| PIN 1                    | +      |
| PIN 2                    | NC S 2 |
| PIN 3                    | -      |
| PIN 4                    | NO S 1 |
| PIN 5                    | PE     |