

## MIRO 6.2 OPTO-COUPLER MODULE

IN: 30 VDC - OUT: 48 VDC / 0,1 A / 500kHz

Transistor 0.1 A



24 V DC

Switching frequency: max. 500 kHz

Spring clamp terminals

### Ürün Linki

örnekleme



Ürün Image farklı olabilir



### Ticari bilgiler

|             |          |
|-------------|----------|
| ECLASS-6.0  | 27371604 |
| ECLASS-6.1  | 27371604 |
| ECLASS-7.0  | 27371604 |
| ECLASS-8.0  | 27371604 |
| ECLASS-9.0  | 27371604 |
| ECLASS-10.1 | 27371604 |

|                                                 |                           |
|-------------------------------------------------|---------------------------|
| ECLASS-11.1                                     | 27371604                  |
| ECLASS-12.0                                     | 27371604                  |
| ETIM-5.0                                        | EC001504                  |
| GTIN                                            | 4048879024372             |
| Gümrük tarife no (gtip)                         | 85414900                  |
| Paket miktarı                                   | 1                         |
| <b>Electrical data   Input</b>                  |                           |
| Input voltage OFF DC min.                       | 0 V                       |
| Input voltage OFF DC max.                       | 7 V                       |
| Input voltage DC min.                           | 10 V                      |
| Input voltage DC max.                           | 30 V                      |
| Current input DC                                | 5,5 mA                    |
| <b>Electrical data   Output</b>                 |                           |
| Switch off delay max.                           | 0,1 µs                    |
| Quiescent current OFF max.                      | 0,25 mA                   |
| Switching frequency ohmic max.                  | 500000 Hz                 |
| Voltage switching DC min.                       | 5 V                       |
| Switching voltage DC max.                       | 48 V                      |
| Switching current min.                          | 0 mA                      |
| Switching current max.                          | 0,1 A                     |
| Voltage drop AC max.                            | 1,2 V                     |
| Voltage drop DC max.                            | 1,2 V                     |
| <b>Diagnostics</b>                              |                           |
| Status indication LED                           | yellow                    |
| <b>Device protection   Electrical</b>           |                           |
| Rated insulation voltage                        | 2750 V                    |
| <b>Device protection   Media</b>                |                           |
| Flame resistance                                | flame retardant           |
| <b>Mechanical data   Material data</b>          |                           |
| Color housing                                   | black                     |
| Material housing                                | Plastic                   |
| <b>Mechanical data   Mounting data</b>          |                           |
| Mounting method                                 | geschnappt                |
| Suitable for mounting type                      | mounting rail, (EN 60715) |
| Height                                          | 91 mm                     |
| Width                                           | 6,2 mm                    |
| Depth                                           | 70 mm                     |
| <b>Environmental characteristics   Climatic</b> |                           |
| Operating temperature min.                      | -20 °C                    |
| Operating temperature max.                      | 60 °C                     |