



EXACT8, 6XM8, 3 POLE PRE-WIRED CABLE

5.0m PUR/PVC 6\*0,34+2\*0,75


6-way, 3-pole  
PUR/PVC  
Further cable lengths on request.  
5.0 m  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료       |          |
|------------|----------|
| ECLASS-6.0 | 27279219 |
| ECLASS-6.1 | 27279219 |
| ECLASS-7.0 | 27279219 |
| ECLASS-8.0 | 27279219 |

|                                          |                                                    |
|------------------------------------------|----------------------------------------------------|
| ECLASS-9.0                               | 27440108                                           |
| ECLASS-10.1                              | 27440108                                           |
| ECLASS-11.1                              | 27440108                                           |
| ECLASS-12.0                              | 27440108                                           |
| ETIM-5.0                                 | EC002585                                           |
| GTIN                                     | 4048879055284                                      |
| 세번부호                                     | 85444290                                           |
| 포장단위                                     | 1                                                  |
| Electrical data   Supply                 |                                                    |
| Operating voltage DC                     | 24 V                                               |
| Current operating per contact max.       | 2 A                                                |
| Total current max.                       | 8 A                                                |
| Industrial communication                 |                                                    |
| Number of signals per port               | 1                                                  |
| Installation   Connection                |                                                    |
| Mounting set                             | M8 x 1                                             |
| Device protection   Electrical           |                                                    |
| Degree of protection (EN IEC 60529)      | IP65, IP67                                         |
| Device protection   Media                |                                                    |
| Flame resistance                         | flame retardant                                    |
| Mechanical data   Material data          |                                                    |
| Material housing                         | Plastic                                            |
| Mechanical data   Mounting data          |                                                    |
| Mounting method                          | Schraubgewinde                                     |
| Environmental characteristics   Climatic |                                                    |
| Operating temperature min.               | -20 °C                                             |
| Operating temperature max.               | 80 °C                                              |
| Additional condition temperature range   | depending on cable quality                         |
| Installation   Cable                     |                                                    |
| STOOW style jacket                       | Hybrid, Signal, Power                              |
| Cable identification                     | 350                                                |
| Cable Type                               | 2                                                  |
| Jacket Color                             | gray                                               |
| Type of Certificate                      | cURus                                              |
| Amount stranding                         | 1                                                  |
| Stranding                                | 8 wires around Core filler twisted                 |
| Filler                                   | yes                                                |
| wire arrangement                         | brown, blue, red, pink, gray, yellow, green, white |
| Cable weigth                             | 94,6 g/m                                           |
| Material jacket                          | PUR                                                |
| Shore hardness jacket                    | 87 ± 5 Shore A                                     |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, silicone-free   |
| Outer-diameter (jacket)                  | 7,8 mm                                             |
| Tolerance outer diameter (sheath)        | ± 5 %                                              |
| Material inner jacket                    | PVC                                                |
| Color (inner jacket)                     | gray                                               |
| Material wire insulation                 | PVC                                                |
| Amount wires                             | 6                                                  |
| Outer diameter insulation                | 1,3 mm                                             |
| Outer diameter tolerance core insulation | ± 5 %                                              |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Shore hardness wire insulation                    | 43 ± 5 Shore D                                       |
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands (wire)                             | 19                                                   |
| Diameter of single wires                          | 0,15 mm                                              |
| Conductor crosssection (wire)                     | 0,34 mm²                                             |
| Traversing distance (C-track)                     | 5 m @ 25 °C                                          |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | Strand class 5                                       |
| Travel speed (C-track)                            | 2                                                    |
| Material wire insulation (Power)                  | PVC                                                  |
| Outer diameter wire insulation (Power)            | 1,8 mm                                               |
| Tolerance outer diameter wire insulation (Power)  | ±5 %                                                 |
| Shore hardness wire insulation (Power)            | 43±5 Shore D                                         |
| Material properties wire insulation (Power)       | good machinability                                   |
| Ingredient freeness wire insulation (Power)       | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands wire (Power)                       | 24                                                   |
| Diameter of single wires (Power)                  | 0,2 mm                                               |
| Wire conductor cross section (Power)              | 0,75 mm²                                             |
| Material conductor wire (Power)                   | Stranded copper wire, bare                           |
| Conductor type wire (Power)                       | Strand class 5                                       |
| Max. rated voltage (conductor - conductor)        | 300 V                                                |
| Max. rated voltage (conductor - ground)           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4 A                                                  |
| Loop resistance                                   | 7,8 A                                                |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                      |
| Electrical resistance coating wire (Power)        | 26 Ω/km @20 °C                                       |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| Flame resistance                                  | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |
| Travel speed (C-track)                            | 2 Mio. @ 25 °C                                       |