



MIRO 6.2 PLUGGABLE COMPL.MODULE OUTPUT RELAY

IN: 125 VAC/DC - OUT: 250 VAC/30VDC / 6 A

1 NO/NC contact
6 A
115 V AC/DC
Spring clamp terminals

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27371601
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-8.0	27371601
ECLASS-9.0	27371601
ECLASS-10.1	27371601

ECLASS-11.1	27371601
ECLASS-12.0	27371601
ETIM-5.0	EC001437
GTIN	4048879021425
Gümrük tarife no (gtip)	85364900
Paket miktarı	1

Electrical data | Input

Input voltage AC min.	88 V
Input voltage AC max.	138 V
Input voltage DC min.	88 V
Input voltage DC max.	138 V
Input current	8 mA
Control voltage AC min.	115 V
Control voltage AC max.	125 V
Control voltage DC min.	115 V
Control voltage DC max.	125 V

Electrical data | Output

Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24 V, 6 A @ 110 V, 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V, 3 A @ 110 V, 1,5 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V, 0,2 A @ 110 V, 0,1 A @ 230 V
Switching frequency max.	10 Hz
Power rating AC max.	1500 VA
Power rating DC max.	180 W
Switching voltage AC max.	250 V
Switching voltage DC max.	30 V
Switching current DC	100 mA
Switching current max.	6 A

Diagnostics

Status indication LED	green
-----------------------	-------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	250 V
Electrical lifetime NC	10000 Cycles
Electrical lifetime NO	30000 Cycles

Device protection | Mechanical

Mechanical endurance	10000000 Cycles
----------------------	-----------------

Mechanical data

Drop-out time max.	4 ms
Response time max.	8 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	93 mm
Width	6,2 mm
Depth	75,6 mm

Environmental characteristics | Climatic

Operating temperature min. -25 °C

Operating temperature max. 60 °C

Connection type 5

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 12

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 11

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 14

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 A 1

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 A 2