

MICO IP67 electronic circuit protection, 4 Channels, 4A

IN: 24 V DC OUT: 24 V DC / 4 A CL2

Mico67 is the perfect electronic overcurrent protection solution for decentralized installations in IP67 protection class. Mico67 is designed for reliable protection of actuators, sensors, DC motors, lighting, fieldbus modules, and also serves as circuit protection. These modules find application in various industries such as mechanical engineering, intralogistics, automotive, packaging, vision systems, and more.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27371802
ECLASS-6.1	27371802
ECLASS-7.0	27371802
ECLASS-8.0	27371802
ECLASS-9.0	27371802
ECLASS-10.1	27371802
ECLASS-11.1	27371802
ECLASS-12.0	27371802
GTIN	4065909074602
세번부호	85363010
포장단위	1
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67
Device protection Mechanical	
Shock resistance (EN IEC 60068-2-27)	50 g, 11 ms
Mechanical data Mounting data	

이 데이터 시트에 포함된 정보는 최대한의 주의로 작성되었습니다.
2024-05-15

Height	34,8 mm
Width	30 mm
Depth	151 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	45 °C
Storage temperature min.	-25 °C
Storage temperature max.	70 °C
Relative humidity max. (operation)	95 % no dew formation
Conformity	
Product standard	EN 61000-6-2 EN 61000-6-3
Connection types	
Connection type 1	Power In
Connection type 3	X1-X4