

### M8 male 0° / M8 female 0° A-cod. snap-in

PUR 3x0.25 ye UL/CSA+drag ch. 1m

Male straight – female straight

M8 (Snap In) – M8 (Snap In), 3-pole




Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

### 제품 링크

#### 일러스트





실제 제품은 이미지와 다를 수 있습니다.



|                                           |                                                                                                     |
|-------------------------------------------|-----------------------------------------------------------------------------------------------------|
| Cable length                              | 1 m                                                                                                 |
| Side 1                                    |                                                                                                     |
| Thread                                    | M8                                                                                                  |
| suitable for corrugated tube (internal Ø) | 6,5 mm                                                                                              |
| 제품자료                                      |                                                                                                     |
| ECLASS-6.0                                | 27061801                                                                                            |
| 세번부호                                      | 85444290                                                                                            |
| 포장단위                                      | 1                                                                                                   |
| Electrical data   Supply                  |                                                                                                     |
| Operating voltage AC max.                 | 50 V                                                                                                |
| Operating voltage DC max.                 | 60 V                                                                                                |
| Operating voltage AC (UL-listed)          | 30 V                                                                                                |
| Operating voltage DC (UL-listed)          | 30 V                                                                                                |
| Current operating per contact max.        | 4 A                                                                                                 |
| Device protection   Electrical            |                                                                                                     |
| Degree of protection (EN IEC 60529)       | IP65                                                                                                |
| Additional condition protection degree    | inserted, locked                                                                                    |
| Pollution Degree                          | 3                                                                                                   |
| Rated surge voltage                       | 1,5 kV                                                                                              |
| Material group (IEC 60664-1)              | I                                                                                                   |
| Mechanical data   Material data           |                                                                                                     |
| Material housing                          | PUR                                                                                                 |
| Mechanical data   Mounting data           |                                                                                                     |
| Looking techniques                        | Snap In                                                                                             |
| Environmental characteristics   Climatic  |                                                                                                     |
| Operating temperature min.                | -25 °C                                                                                              |
| Operating temperature max.                | 85 °C                                                                                               |
| Additional condition temperature range    | depending on cable quality                                                                          |
| Important installation notes              |                                                                                                     |
| Note on strain relief                     | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties. |

Note on bending radius

**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

| Conformity                                        |                                                                |
|---------------------------------------------------|----------------------------------------------------------------|
| Product standard                                  | DIN EN 61076-2-114 (M8)                                        |
| Installation   Cable                              |                                                                |
| Cable identification                              | 030                                                            |
| Cable Type                                        | 3                                                              |
| Jacket Color                                      | yellow                                                         |
| Type of Certificate                               | cURus                                                          |
| Amount stranding                                  | 1                                                              |
| Stranding                                         | 3 wires twisted                                                |
| wire arrangement                                  | brown, black, blue                                             |
| Traversing distance (C-track)                     | 10 m @ 25 °C   horizontal                                      |
| Cable weight                                      | 26,4 g/m                                                       |
| Material jacket                                   | PUR                                                            |
| Shore hardness jacket                             | 90 ± 5 Shore A                                                 |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                           | 4,1 mm                                                         |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                          |
| Material wire insulation                          | PP                                                             |
| Amount wires                                      | 3                                                              |
| Outer diameter insulation                         | 1,25 mm                                                        |
| Outer diameter tolerance core insulation          | ± 5 %                                                          |
| Shore hardness wire insulation                    | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                             | 32                                                             |
| Diameter of single wires                          | 0,1 mm                                                         |
| Conductor crosssection (wire)                     | 0,25 mm <sup>2</sup>                                           |
| Material conductor wire                           | Stranded copper wire, bare                                     |
| Conductor type (wire)                             | strand class 6                                                 |
| Nominal voltage AC max.                           | 300 V                                                          |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                   | 4,5 A                                                          |
| Electrical resistance line constant wire          | 79 Ω/km @ 20 °C                                                |
| AC withstand voltage (wire - wire)                | 2,5 kV @ 60 s                                                  |
| Power frequency withstand voltage (wire - jacket) | 2,5 kV @ 60 s                                                  |
| Min. operating temperature (static)               | -40 °C                                                         |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                              |
| Operating temperature min. (dynamic)              | -25 °C                                                         |
| Operating temperature max. (dynamic)              | 80 °C / 90 °C @ 10000 h Operation                              |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090            |
| chemical resistance                               | Good, application-related testing                              |
| Gasoline resistance                               | Good, application-related testing                              |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (fixed)                            | 5 x Outer diameter                                             |
| Bending radius (dynamic)                          | 10 x Outer diameter                                            |
| Travel speed (C-track)                            | 10 Mio. @ 25 °C                                                |
| No. of torsion cycles                             | 2 Mio.                                                         |
| Torsion stress                                    | ± 180 °/m                                                      |
| Torsion speed                                     | 35 cycles/min                                                  |