



RM 14/230V AC OUTPUT RELAY

IN: 230 VAC/DC - OUT: 250 VAC/DC / 2 A

1 relay; 4 NO/NC contacts
2 A
230 V AC
Screw terminals

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-8.0	27371601
ECLASS-9.0	27371601
ECLASS-10.1	27371601

ECLASS-11.1	27371601
ECLASS-12.0	27371601
ETIM-5.0	EC001437
GTIN	4048879027625
Gümrük tarife no (gtip)	85364900
Paket miktarı	1
Electrical data Input	
Input voltage AC	230 V
Input voltage AC min.	195 V
Input voltage AC max.	250 V
Input voltage DC	230 V
Input voltage DC min.	195 V
Input voltage DC max.	250 V
Input current	10 mA
Electrical data Output	
Utilization category DC-13 (EN IEC 60947-5-1)	0,8 A @ 24 V, 0,01 A @ 230 V
Additional condition switching frequency	with load
Switching frequency max.	0,1 Hz
Power rating AC max.	125 VA
Power rating DC max.	60 W
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	0,1 mA
Switching current max.	2 A
Switching capacity AC-12 (EN IEC 60947-5-1)	2 A (24 V AC); 0.5 A (230 V AC)
Switching capacity AC-15 (EN IEC 60947-5-1)	1 A (24 V AC); 0.1 A (230 V AC)
Diagnostics	
Status indication LED	red
Device protection	
Condition lifetime	load-dependent
Device protection Electrical	
Rated surge voltage	1,5 kV
Electrical lifetime	50000000 Cycles
Device protection Mechanical	
Mechanical endurance	50000000 Cycles
Mechanical data	
Drop-out time max.	20 ms
Response time max.	10 ms
Bounce time max.	2 ms
Mechanical data Material data	
Material contact	Ag Au
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)
Height	75 mm
Width	22,5 mm
Depth	102 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	55 °C

Connection type 4

Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	3
PIN 1	12
PIN 2	11
PIN 3	14
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	3
PIN 1	31
PIN 2	32
PIN 3	34
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	4
PIN 1	21
PIN 2	24
PIN 3	22
PIN 4	41
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	4
PIN 1	A 1
PIN 2	A 2
PIN 3	44
PIN 4	42