

Gateway CC-Link/AS-i, 1 Master, P24

Spec. 3.0, Power 24

AS-Interface/CC-Link

Power 24V

Specification 3.0

Current manuals, GSD/type data can be downloaded at: www.murrelektronik.com

Other gateways on request.

Gateway-Singlemaster

AS-Interface data decoupling integrated

AS-Interface duplicate address detection


AS-Interface EMC detector integrated

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27242608
ECLASS-6.1	27242608
ECLASS-7.0	27242608
ECLASS-8.0	27242608
ECLASS-9.0	27242608
ECLASS-10.1	27242608
ECLASS-11.1	27242608
ECLASS-12.0	27242608
ETIM-5.0	EC001604
GTIN	4048879661683
Gümrük tarife no (gtip)	85176200
Paket miktarı	1

Electrical data

Rated operating current AS-Interface max.	250 mA
Security level	PELV

Electrical data | Supply

Bu veri sayfasındaki bilgiler en büyük özenle hazırlanmıştır.

Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmalî sınırlıdır. Sürüm: 2024-05-21

Murrelektronik GmbH | Falkenstrasse 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Operating voltage DC	24 V
Operating voltage DC min.	20 V
Operating voltage DC max.	30,6 V
Industrial communication	
Supported protocol	CC-Link
Industrial communication Bus data	
Automatic baudrate detection	no
Baud rate min.	156 kBaud
Baud rate max.	10 MBaud
Industrial communication AS-Interface	
AS-i specification	V3.0
Number of slaves max.	62
Diagnostic interface serial	None
Cycle time AS-i	150 µs × (number of slaves + 2)
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	500 V
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	120 mm
Width	85 mm
Depth	83 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Conformity	
Product standard	EN 61131-2, EN 62026-2