

MVP12 plastic DI16 IOL HUB

IO-Link Version 1.1

Compact module



IO-Link V1.1

Connection cables are in the online shop under "Connection Technology".

Housing fully potted.

Ürün Linki**örnekleme**

Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
GTIN	4048879695688
Gümrük tarife no (gtip)	85369010
Paket miktarı	1

Electrical data | Input

Type input	PNP (EN 61131-2) Type 3
Input filter time	1 ms

Industrial communication | IO-Link

IO-Link type	Device
Port Class	A
IO-Link revision ID	V1.1
IO-Link transmission rate	COM2 (38.4 kbit/s)

IO-Link cycle time min. 2,3 ms

Diagnostics

Diagnostic via LED	per module and channel
IO-Link events	No voltage, Undervoltage supply
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

Device protection | Electrical

Degree of protection (EN IEC 60529) IP67

Mechanical data | Mounting data

Suitable for mounting type	2-hole screw mounting
Height	126 mm
Width	50 mm
Depth	34,5 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	70 °C

Connection type 4

Connection type 1	X0-X7
Connection type 2	X0-X7
Connection type 3	XZ1
Connection type 4	XZ1
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	24 V DC (US)
PIN 2	DI
PIN 3	0 V
PIN 4	DI
PIN 5	n.c.
Family construction form	M12
Gender	female
Coding	A
No. of poles	5
PIN 1	24 V DC US
PIN 2	DI
PIN 3	0 V
PIN 4	DI
PIN 5	n.c.
Family construction form	M12
Gender	male
Coding	A
No. of poles	5
PIN 1	24 V DC US
PIN 2	n.c.
PIN 3	0 V
PIN 4	IO-Link
PIN 5	n.c.

Family construction form	M12
Gender	male
Coding	A
No. of poles	5
PIN 1	24 V DC (US)
PIN 2	n.c.
PIN 3	0 V
PIN 4	IO-Link
PIN 5	n.c.