

## MEN POWER SUPPLY 1/2-PHASE, SMOOTHED

IN: 230/400+/-15VAC OUT: :24V/7,5ADC

Current: 7.5 A



Output rating: 180 W

This power supply units meet the (EN 61000-3-2) standard for harmonic current.

Condensation not permitted

### Ürün Linki

#### örnekleme



Ürün Image farklı olabilir



#### Ticari bilgiler

|             |          |
|-------------|----------|
| ECLASS-6.0  | 27049002 |
| ECLASS-6.1  | 27049002 |
| ECLASS-7.0  | 27049002 |
| ECLASS-8.0  | 27049002 |
| ECLASS-9.0  | 27040701 |
| ECLASS-10.1 | 27040701 |

|                                                 |                                   |
|-------------------------------------------------|-----------------------------------|
| ECLASS-11.1                                     | 27040701                          |
| ECLASS-12.0                                     | 27040701                          |
| ETIM-5.0                                        | EC002540                          |
| GTIN                                            | 4048879080002                     |
| Gümrük tarife no (gtip)                         | 85044095                          |
| Paket miktarı                                   | 1                                 |
| <b>Electrical data</b>                          |                                   |
| Security level                                  | SELV                              |
| <b>Electrical data   Supply</b>                 |                                   |
| Power frequency                                 | 50 ... 60 Hz                      |
| <b>Electrical data   Input</b>                  |                                   |
| Fuse protection 1 primary side external         | 2 A @230 V AC                     |
| Fuse protection 2 primary side external         | 1,25 A @400 V AC                  |
| Input voltage 1 AC                              | 230 V                             |
| Input voltage 1 AC min.                         | 195,5 V                           |
| Input voltage 1 AC max.                         | 264,5 V                           |
| Input voltage 2 AC                              | 400 V                             |
| Input voltage 2 AC min.                         | 340 V                             |
| Input voltage 2 AC max.                         | 460 V                             |
| Input current at input voltage 1 AC             | 1,44 A                            |
| Input current at input voltage 2 AC             | 0,84 A                            |
| <b>Electrical data   Output</b>                 |                                   |
| Fuse protection secondary side external         | 15 A                              |
| Output suppression                              | LED, Screening capacitor, VDR     |
| Output voltage DC                               | 24 V                              |
| Output voltage adjustable                       | no                                |
| Output current max.                             | 9 A                               |
| Type of secondary fuse                          | Flat fuse FKS                     |
| Ripple max.                                     | 5 %                               |
| <b>Mechanical data   Mounting data</b>          |                                   |
| Suitable for mounting type                      | Schlüssellochabhängung            |
| Mounting dimension a                            | 86,5 mm                           |
| Mounting dimension b                            | 80,5 mm                           |
| Mounting dimension c                            | 5,8 mm                            |
| Height                                          | 103 mm                            |
| Width                                           | 105 mm                            |
| Depth                                           | 150,5 mm                          |
| <b>Environmental characteristics   Climatic</b> |                                   |
| Operating temperature min.                      | -20 °C                            |
| Operating temperature max.                      | 60 °C                             |
| Derating from                                   | 40 °C                             |
| <b>Conformity</b>                               |                                   |
| Product standard                                | EN 61558-2-6, EN 62041 category I |
| EMC                                             | EN 55011 B, EN 61000-3-2          |
| <b>Connection type 3</b>                        |                                   |
| Connection                                      | Screw terminals SK                |
| Family construction form                        | terminal                          |
| Gender                                          | female                            |
| Color contact carrier                           | metallic                          |
| No. of poles                                    | 1                                 |
| PIN 1                                           | PE                                |

|                          |                    |
|--------------------------|--------------------|
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 3                  |
| PIN 1                    | +                  |
| PIN 2                    | -                  |
| PIN 3                    | -                  |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 5                  |
| PIN 1                    | + 15 V             |
| PIN 3                    | - 15 V             |
| PIN 4                    | 230 V              |
| PIN 5                    | 400 V              |