

EMPARRO CAP BUFFER MODULE

IN: 24VDC OUT: 24VDC/20A for max. 1A/40s



INPUT: 24 V DC (SELV/PELV)

OUTPUT: max. 20 A

1.0 s (20 A); 40 s (1 A)

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27049190
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040705
ECLASS-10.1	27040705

ECLASS-11.1	27040705
ECLASS-12.0	27040705
ETIM-5.0	EC002584
GTIN	4048879436700
Gümrük tarife no (gtip)	85322900
Paket miktarı	1
Electrical data Input	
Input voltage DC min.	21,6 V
Input voltage DC max.	26,4 V
Max. inrush current	25 A
Charging current max.	3 A
Charging time max.	75 s
Efficiency	90 %
Electrical data Output	
Output voltage DC min.	19 V
Output voltage DC max.	25,5 V
Output voltage adjustable	yes
Output current buffer operation	65 A
Output current max.	20 A
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Tragschiene TH35-7.5/TH35-15, (EN 60715)
Height	123 mm
Width	65 mm
Depth	138 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	60 °C
Connection type 2	
Connection type 1	Alarm
Connection type 2	Input / Output
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	13
PIN 2	14
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	-
PIN 2	-
PIN 3	+
PIN 4	+