



MIRO 6.2 OUTPUT RELAY WITH TOGGLE SWITCH

IN: 24 VAC/DC - OUT: 250 VAC/DC / 6 A


1 NO contact
6 A
24 V AC/DC
with protected H-O-A toggle switch
Screw terminals
LED (red/green)
safe separation (EN 60947-1)

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27371601
ECLASS-6.1	27371601
ECLASS-7.0	27371601

ECLASS-8.0	27371601
ECLASS-9.0	27371601
ECLASS-10.1	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ETIM-5.0	EC001437
GTIN	4048879024693
Gümrük tarife no (gtip)	85364900
Paket miktarı	1

Electrical data | Input

Input voltage AC	24 V
Input voltage AC min.	19,2 V
Input voltage AC max.	28 V
Input voltage DC	24 V
Input voltage DC min.	19,2 V
Input voltage DC max.	28 V
Input current	7 mA

Electrical data | Output

Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24, 6 A @ 110 V, 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V, 3 A @ 110 V, 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V, 0,2 A @ 110 V, 0,1 A @ 230 V
Switching frequency max.	10 Hz
Power rating AC max.	1500 VA
Power rating DC max.	120 W
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	100 mA
Switching current max.	6 A

Diagnostics

Status indication LED	green, red
-----------------------	------------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Rated surge voltage	4 kV
Electrical lifetime	20000000 Cycles

Device protection | Mechanical

Mechanical endurance	20000000 Cycles
----------------------	-----------------

Mechanical data

Drop-out time max.	20 ms
Response time max.	8 ms
Bounce time max.	2 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	91 mm
Width	6,2 mm
Depth	71 mm

Environmental characteristics | Climatic

Operating temperature min. -20 °C

Operating temperature max. 55 °C

Connection type 5

Connection Screw terminals SK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 A 2

Connection Screw terminals SK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 A 3

Connection Screw terminals SK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 A 1

Connection Screw terminals SK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 14

Connection Screw terminals SK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 13