



MIRO 6.2 OPTO-COUPLER MODULE

IN: 125 VAC - OUT: 110 VDC / 0.5A

Transistor 0.5 A
Spring clamp terminals**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27371601
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-8.0	27371604
ECLASS-9.0	27371604
ECLASS-10.1	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604

ETIM-5.0	EC001504
GTIN	4048879024327
Gümrük tarife no (gtip)	85414900
Paket miktarı	1

Electrical data | Input

Input voltage AC	125 V
Input voltage AC min.	24 V
Input voltage AC max.	156 V
Input voltage OFF AC min.	0 V
Input voltage OFF AC max.	4,5 V
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	5 V
Input voltage DC	110 V
Input voltage DC min.	24 V
Input voltage DC max.	137 V
Input current min.	1,1 mA
Input current max.	5 mA

Electrical data | Output

Output current min.	0,001 A
Output current max.	0,5 A
Quiescent current OFF max.	0,02 mA
Switching frequency max.	2,5 Hz
Switching voltage DC	110 V

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Insulation test voltage input - output	4 kV

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data | Material data

Color housing	black
Material housing	Plastic

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	78 mm
Width	6,2 mm
Depth	65 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Derating from	40 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C