



## MIRO 6.2 pluggable compl. Module Optocoupler

IN: 24 VDC - OUT: 24 VDC / 6 A

Transistor 6 A  
24 V DC  
Spring clamp terminals  
Complete module

### Ürün Linki

#### örnekleme



Ürün Image farklı olabilir



#### Ticari bilgiler

|             |          |
|-------------|----------|
| ECLASS-6.0  | 27371604 |
| ECLASS-6.1  | 27371604 |
| ECLASS-7.0  | 27371604 |
| ECLASS-8.0  | 27371604 |
| ECLASS-9.0  | 27371604 |
| ECLASS-10.1 | 27371604 |

|                                                 |               |
|-------------------------------------------------|---------------|
| ECLASS-11.1                                     | 27371604      |
| ECLASS-12.0                                     | 27371604      |
| ETIM-5.0                                        | EC001504      |
| GTIN                                            | 4048879532747 |
| Gümrük tarife no (gtip)                         | 85365005      |
| Paket miktarı                                   | 1             |
| <b>Electrical data   Input</b>                  |               |
| Input voltage DC                                | 24 V          |
| Input voltage DC min.                           | 18 V          |
| Input voltage DC max.                           | 30 V          |
| Input current                                   | 9 mA          |
| <b>Electrical data   Output</b>                 |               |
| Switch off delay max.                           | 31 µs         |
| Forward voltage max.                            | 240 mV        |
| Switching frequency inductive max.              | 50 Hz         |
| Switching frequency ohmic max.                  | 500 Hz        |
| Voltage switching DC min.                       | 3 V           |
| Switching voltage DC max.                       | 30 V          |
| Switching current min.                          | 10 mA         |
| Switching current max.                          | 6 A           |
| <b>Diagnostics</b>                              |               |
| Status indication LED                           | yellow        |
| <b>Device protection   Electrical</b>           |               |
| Degree of protection (EN IEC 60529)             | IP20          |
| Rated insulation voltage                        | 50 V          |
| Rated surge voltage                             | 2,5 kV        |
| <b>Mechanical data   Mounting data</b>          |               |
| Mounting method                                 | inserted      |
| Height                                          | 93 mm         |
| Width                                           | 6,2 mm        |
| Depth                                           | 75,6 mm       |
| <b>Environmental characteristics   Climatic</b> |               |
| Operating temperature min.                      | -25 °C        |
| Operating temperature max.                      | 50 °C         |