

**M12 female 0° B-cod. with cable shielded**

PUR 1x2xAWG23 shielded vt UL/CSA+robot 3m

PROFIBUS

Female straight

M12, 2-pole

B-coded

shielded



Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.


Further cable lengths on request.

**Ürün Linki**

örnekleme



Ürün Image farklı olabilir



Cable length

3 m

Side 1

|                                     |                   |
|-------------------------------------|-------------------|
| Tightening torque                   | 0,6 Nm            |
| Mounting method                     | inserted, screwed |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Coding                              | B                 |
| Material                            | PUR               |
| Width across flats                  | SW13              |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67 |

**Side 2**

|                           |       |
|---------------------------|-------|
| Stripping length (jacket) | 20 mm |
|---------------------------|-------|

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27061801      |
| ECLASS-6.1              | 27060307      |
| ECLASS-7.0              | 27060307      |
| ECLASS-8.0              | 27060307      |
| ECLASS-9.0              | 27060307      |
| ECLASS-10.1             | 27060307      |
| ECLASS-11.1             | 27060307      |
| ECLASS-12.0             | 27060307      |
| ETIM-5.0                | EC001855      |
| GTIN                    | 4048879478380 |
| Gümrük tarife no (gtip) | 85444290      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 60 V |
| Operating voltage DC max.          | 60 V |
| Operating voltage AC (UL-listed)   | 30 V |
| Operating voltage DC (UL-listed)   | 30 V |
| Current operating per contact max. | 4 A  |

**Installation | Connection**

|                           |         |
|---------------------------|---------|
| Stripping length (jacket) | 20 mm   |
| Mounting set              | M12 x 1 |

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data | Material data**

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

**Important installation notes**

|                       |                                                                                                     |
|-----------------------|-----------------------------------------------------------------------------------------------------|
| Note on strain relief | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties. |
|-----------------------|-----------------------------------------------------------------------------------------------------|

Note on bending radius

**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.**Conformity**

Product standard DIN EN 61076-2-101 (M12)

**Installation | Cable**

|                                          |                                                                |
|------------------------------------------|----------------------------------------------------------------|
| Cable identification                     | 843                                                            |
| Jacket Color                             | green                                                          |
| Type of Certificate                      | cURus                                                          |
| Amount stranding                         | 1                                                              |
| Stranding                                | 2 wires with 2 Filler twisted                                  |
| Cable shielding (type)                   | copper braid, tinned                                           |
| Cable shielding (coverage)               | 85 %                                                           |
| Banding                                  | Fleece, Foil                                                   |
| Filler                                   | yes                                                            |
| Drain wire (cross-section)               | 0,14 mm <sup>2</sup>                                           |
| wire arrangement                         | brown, white, red, blue, pink, gray, yellow, green             |
| Traversing distance (C-track)            | 10 m @ 25 °C   horizontal                                      |
| Cable weight                             | 79,2 g/m                                                       |
| Material jacket                          | PUR                                                            |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                  | 8,1 mm                                                         |
| Tolerance outer diameter (sheath)        | ± 5 %                                                          |
| Material wire insulation                 | PP                                                             |
| Amount wires                             | 2                                                              |
| Outer diameter insulation                | 2,6 mm                                                         |
| Outer diameter tolerance core insulation | ± 5 %                                                          |
| Shore hardness wire insulation           | 55 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation      | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                    | 19                                                             |
| Diameter of single wires                 | 23 AWG                                                         |
| Conductor crosssection (wire)            | 23 AWG                                                         |
| Drain wire (cross-section)               | 0,14 mm <sup>2</sup>                                           |
| Material conductor wire                  | Stranded copper wire, bare                                     |
| Nominal voltage AC max.                  | 300 V                                                          |
| Current load capacity (standard)         | to DIN VDE 0298-4                                              |
| Current load capacity min. wire          | 3 A                                                            |
| Electrical resistance line constant wire | 59,4 Ω/km                                                      |
| AC withstand voltage (wire - wire)       | 1,2 kV @ 60 s                                                  |
| AC withstand voltage (wire - shield)     | 0,8 kV @ 60 s                                                  |
| Min. operating temperature (static)      | -50 °C                                                         |
| Max. operating temperature (fixed)       | 80 °C                                                          |
| Operating temperature min. (dynamic)     | -30 °C                                                         |
| Operating temperature max. (dynamic)     | 80 °C                                                          |
| Flame resistance                         | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090            |
| chemical resistance                      | Good, application-related testing                              |
| Gasoline resistance                      | Good, application-related testing                              |
| Oil resistance                           | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (installation)            | x Outer diameter                                               |
| Bending radius (fixed)                   | 5 x Outer diameter                                             |
| Bending radius (dynamic)                 | 7,5 x Outer diameter                                           |
| Travel speed (C-track)                   | 2 Mio. @ 25 °C                                                 |