

**M23 female 0° with cable**

PUR 8x0.34+3x0.75 gy drag ch. 10m

Female straight

M23, 12-pole


11-pole used

for 8-way distribution box, 4-pole



Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**Ürün Linki****örnekleme**

|    |       |
|----|-------|
| 1  | WH    |
| 2  | GN    |
| 3  | YE    |
| 4  | GY    |
| 5  | PK    |
| 6  | RD    |
| 7  | BK    |
| 8  | VT    |
| 9  | BU    |
| 10 |       |
| 11 | BN    |
| 12 | GN YE |



Ürün Image farklı olabilir

Cable length 10 m

**Side 1**

|                          |                   |
|--------------------------|-------------------|
| Tightening torque        | 2 Nm              |
| Mounting method          | inserted, screwed |
| Family construction form | M23               |
| Thread                   | M23 x 1           |
| Material                 | PUR               |

|                                                 |                                                                                                                                                       |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Width across flats                              | SW27                                                                                                                                                  |
| Degree of protection (EN IEC 60529)             | IP65, IP67                                                                                                                                            |
| <b>Ticari bilgiler</b>                          |                                                                                                                                                       |
| ECLASS-6.0                                      | 27279218                                                                                                                                              |
| ECLASS-7.0                                      | 27279218                                                                                                                                              |
| ECLASS-8.0                                      | 27279218                                                                                                                                              |
| ECLASS-9.0                                      | 27060311                                                                                                                                              |
| ECLASS-10.1                                     | 27060311                                                                                                                                              |
| ECLASS-11.1                                     | 27060311                                                                                                                                              |
| ECLASS-12.0                                     | 27060311                                                                                                                                              |
| ETIM-5.0                                        | EC001855                                                                                                                                              |
| GTIN                                            | 4048879188371                                                                                                                                         |
| Gümrük tarife no (gtip)                         | 85444290                                                                                                                                              |
| Paket miktarı                                   | 1                                                                                                                                                     |
| <b>Electrical data   Supply</b>                 |                                                                                                                                                       |
| Operating voltage AC max.                       | 125 V                                                                                                                                                 |
| Operating voltage DC max.                       | 125 V                                                                                                                                                 |
| Current operating per contact max.              | 7,5 A                                                                                                                                                 |
| <b>Installation   Connection</b>                |                                                                                                                                                       |
| Mounting set                                    | M23 x 1                                                                                                                                               |
| <b>Device protection   Electrical</b>           |                                                                                                                                                       |
| Additional condition protection degree          | inserted, screwed                                                                                                                                     |
| <b>Mechanical data   Material data</b>          |                                                                                                                                                       |
| Coating of fitting                              | nickel plated                                                                                                                                         |
| Material screw connection                       | Brass                                                                                                                                                 |
| <b>Mechanical data   Mounting data</b>          |                                                                                                                                                       |
| Mounting method                                 | inserted, screwed                                                                                                                                     |
| <b>Environmental characteristics   Climatic</b> |                                                                                                                                                       |
| Operating temperature min.                      | -25 °C                                                                                                                                                |
| Operating temperature max.                      | 85 °C                                                                                                                                                 |
| Additional condition temperature range          | depending on cable quality                                                                                                                            |
| <b>Important installation notes</b>             |                                                                                                                                                       |
| Note on strain relief                           | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                          | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| <b>Installation   Cable</b>                     |                                                                                                                                                       |
| wire arrangement                                | white, violet, (green, yellow, gray, pink, red, black, brown, blue, green-yellow)                                                                     |
| Cable identification                            | 362                                                                                                                                                   |
| Cable Type                                      | 2                                                                                                                                                     |
| Function cable                                  | Hybrid, Signal, Power                                                                                                                                 |
| Jacket Color                                    | gray                                                                                                                                                  |
| Type of Certificate                             | cURus                                                                                                                                                 |
| Amount stranding                                | 1                                                                                                                                                     |
| Stranding                                       | 2 wires with Filler twisted                                                                                                                           |
| Amount stranding (type 2)                       | 1                                                                                                                                                     |
| Stranding (type 2)                              | 9 wires around Stranding combination twisted                                                                                                          |
| Filler                                          | yes                                                                                                                                                   |
| wire arrangement                                | white, violet, (green, yellow, gray, pink, red, black, brown, blue, green-yellow)                                                                     |
| Cable weight                                    | 115,5 g/m                                                                                                                                             |
| Material jacket                                 | PUR                                                                                                                                                   |
| Shore hardness jacket                           | 87 ± 5 Shore A                                                                                                                                        |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, silicone-free     |
| Outer-diameter (jacket)                           | 8,1 mm                                               |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                |
| Material inner jacket                             | PVC                                                  |
| Color (inner jacket)                              | gray                                                 |
| Material wire insulation                          | PVC                                                  |
| Amount wires                                      | 8                                                    |
| Outer diameter insulation                         | 1,3 mm                                               |
| Outer diameter tolerance core insulation          | ± 5 %                                                |
| Shore hardness wire insulation                    | 43 ± 5 Shore D                                       |
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands (wire)                             | 19                                                   |
| Diameter of single wires                          | 0,15 mm                                              |
| Conductor crosssection (wire)                     | 0,34 mm <sup>2</sup>                                 |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | Strand class 5                                       |
| Material wire insulation (Power)                  | PVC                                                  |
| Outer diameter wire insulation (Power)            | 1,8 mm                                               |
| Tolerance outer diameter wire insulation (Power)  | ±5 %                                                 |
| Shore hardness wire insulation (Power)            | 43±5 Shore D                                         |
| Material properties wire insulation (Power)       | good machinability                                   |
| Ingredient freeness wire insulation (Power)       | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount wires (Power)                              | 3                                                    |
| Amount strands wire (Power)                       | 24                                                   |
| Diameter of single wires (Power)                  | 0,2 mm                                               |
| Wire conductor cross section (Power)              | 0,75 mm <sup>2</sup>                                 |
| Material conductor wire (Power)                   | Stranded copper wire, bare                           |
| Conductor type wire (Power)                       | Strand class 5                                       |
| Max. rated voltage (conductor - conductor)        | 300 V                                                |
| Max. rated voltage (conductor - ground)           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4 A                                                  |
| Current carrying capacity min. wire (Power)       | 7,8 A                                                |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                      |
| Electrical resistance coating wire (Power)        | 26 Ω/km @20 °C                                       |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| Flame resistance                                  | UL 1581 § 1090   IEC 60332-2-2   UL 1581 § 1100 FT2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |
| No. of bending cycles (C-track)                   | 2 Mio. @ 25 °C                                       |
| Traversing distance (C-track)                     | 5 m @ 25 °C                                          |
| Travel speed (C-track)                            | 10 m/s @ 25 °C                                       |