

**M12 male 0° / M8 female 90° A-cod.**

PUR 3x0.25 bk UL/CSA 0.45m



**⚠ NOTICE ⚠****PRODUCT IS DISCONTINUED. PLEASE HAVE A LOOK AT THE ALTERNATIVE PRODUCTS.**

Male straight – female 90°


M12 – M8, 3-pole


Art-No. 7005 - M12/M8 Lite - (plastic hexagonal screw) on request  
with cable sleeves

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.**Ürün Linki****örnekleme**

|   |    |   |
|---|----|---|
| 1 | BN | 1 |
|   |    | 2 |
| 3 | BU | 3 |
| 4 | BK | 4 |





Ürün Image farklı olabilir



Cable length 0,45 m

#### Side 1

|                                           |                   |
|-------------------------------------------|-------------------|
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M12               |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 10 mm             |
| Coding                                    | A                 |
| Material                                  | PUR               |
| No. of poles                              | 3                 |
| Width across flats                        | SW13              |
| Degree of protection (EN IEC 60529)       | IP67              |

#### Side 2

|                                           |                   |
|-------------------------------------------|-------------------|
| Tightening torque                         | 0,4 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M8                |
| Thread                                    | M8 x 1            |
| suitable for corrugated tube (internal Ø) | 6,5 mm            |
| Coding                                    | A                 |
| Material                                  | PUR               |
| No. of poles                              | 3                 |
| Width across flats                        | SW9               |
| Degree of protection (EN IEC 60529)       | IP67              |

#### Ticari bilgiler

|             |          |
|-------------|----------|
| ECLASS-6.0  | 27279218 |
| ECLASS-6.1  | 27279218 |
| ECLASS-7.0  | 27279218 |
| ECLASS-8.0  | 27279218 |
| ECLASS-9.0  | 27060311 |
| ECLASS-10.1 | 27060311 |

|                                                 |                                                   |
|-------------------------------------------------|---------------------------------------------------|
| ECLASS-11.1                                     | 27060311                                          |
| ECLASS-12.0                                     | 27060311                                          |
| ETIM-5.0                                        | EC001855                                          |
| GTIN                                            | 4048879161053                                     |
| Gümrük tarife no (gtip)                         | 85444290                                          |
| Paket miktarı                                   | 1                                                 |
| <b>Electrical data   Supply</b>                 |                                                   |
| Operating voltage AC max.                       | 50 V                                              |
| Operating voltage DC max.                       | 60 V                                              |
| Operating voltage AC (UL-listed)                | 30 V                                              |
| Operating voltage DC (UL-listed)                | 30 V                                              |
| Current operating per contact max.              | 4 A                                               |
| <b>Device protection   Electrical</b>           |                                                   |
| Additional condition protection degree          | inserted, screwed                                 |
| Pollution Degree                                | 3                                                 |
| Rated surge voltage                             | 1,5 kV                                            |
| Material group (IEC 60664-1)                    | I                                                 |
| <b>Mechanical data   Material data</b>          |                                                   |
| Coating housing                                 | Copper alloy                                      |
| Coating locking                                 | Nickeled                                          |
| Coating of fitting                              | nickel plated                                     |
| Material gasket                                 | FKM                                               |
| Locking material                                | Zinc die-casting                                  |
| Material screw connection                       | Zinc die-casting                                  |
| <b>Mechanical data   Mounting data</b>          |                                                   |
| Mounting method                                 | inserted, screwed, Shaking protection             |
| <b>Environmental characteristics   Climatic</b> |                                                   |
| Operating temperature min.                      | -25 °C                                            |
| Operating temperature max.                      | 85 °C                                             |
| Additional condition temperature range          | depending on cable quality                        |
| <b>Conformity</b>                               |                                                   |
| Product standard                                | DIN EN 61076-2-101 (M12), DIN EN 61076-2-114 (M8) |
| <b>Installation   Cable</b>                     |                                                   |
| Cable identification                            | 620                                               |
| Cable Type                                      | 2                                                 |
| Jacket Color                                    | black                                             |
| Type of Certificate                             | cURus                                             |
| Amount stranding                                | 1                                                 |
| Stranding                                       | 3 wires twisted                                   |
| wire arrangement                                | brown, black, blue                                |
| Cable weight                                    | 26,62 g/m                                         |
| Material jacket                                 | PUR                                               |
| Shore hardness jacket                           | 85 ± 5 Shore A                                    |
| Freedom from ingredients (jacket)               | lead-free, cadmium-free, CFC-free, silicone-free  |
| Outer-diameter (jacket)                         | 4,3 mm                                            |
| Tolerance outer diameter (sheath)               | ± 5 %                                             |
| Material wire insulation                        | PVC                                               |
| Amount wires                                    | 3                                                 |
| Outer diameter insulation                       | 1,25 mm                                           |
| Outer diameter tolerance core insulation        | ± 5 %                                             |
| Shore hardness wire insulation                  | 43 ± 5 Shore D                                    |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands (wire)                             | 32                                                   |
| Diameter of single wires                          | 0,1 mm                                               |
| Conductor crosssection (wire)                     | 0,25 mm²                                             |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | strand class 6                                       |
| Traversing distance (C-track)                     | 5 m @ 25 °C   horizontal                             |
| Travel speed (C-track)                            | 2 Mio. @ 25 °C                                       |
| Nominal voltage AC max.                           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4,5 A                                                |
| Electrical resistance line constant wire          | 79 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 80 °C                                                |
| UV resistance                                     | DIN EN ISO 4892-2 A                                  |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                            | 10 x Outer diameter                                  |
| Bending radius (dynamic)                          | 15 x Outer diameter                                  |