

**M12 male 90° / M12 female 90° A-cod.**

PUR 5x0.34 bk UL/CSA 0.3m

**⚠ NOTICE ⚠**

**PRODUCT IS DISCONTINUED. PLEASE HAVE A LOOK AT THE ALTERNATIVE PRODUCTS.**

Male 90° – female 90°

M12 – M12, 5-pole

Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.


**Ürün Linki**


örnekleme




|   |                |     |
|---|----------------|-----|
| 1 | brown (+)      | C 1 |
| 2 | white (N/C)    | C 2 |
| 4 | black (N/O)    | C 4 |
| 3 | blue (-)       | C 3 |
| 5 | gn/ye (* gray) | C 5 |

(\* for cable type 126, 732, 219, 619)





Ürün Image farklı olabilir



Cable length 0,3 m

**Side 1**

|                                           |                   |
|-------------------------------------------|-------------------|
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Family construction form                  | M12               |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 10 mm             |
| Coding                                    | A                 |
| Material                                  | PUR               |
| Width across flats                        | SW13              |
| Degree of protection (EN IEC 60529)       | IP66K, IP67       |

**Side 2**

|                                           |                   |
|-------------------------------------------|-------------------|
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Family construction form                  | M12               |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 10 mm             |
| Coding                                    | A                 |
| Material                                  | PUR               |
| Width across flats                        | SW13              |
| Degree of protection (EN IEC 60529)       | IP66K, IP67       |

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27279218      |
| ECLASS-6.1              | 27279218      |
| ECLASS-7.0              | 27279218      |
| ECLASS-8.0              | 27279218      |
| ECLASS-9.0              | 27060311      |
| ECLASS-10.1             | 27060311      |
| ECLASS-11.1             | 27060311      |
| ECLASS-12.0             | 27060311      |
| ETIM-5.0                | EC001855      |
| GTIN                    | 4048879172097 |
| Gümrük tarife no (gtip) | 85444290      |

Paket miktarı 1

**Electrical data | Supply**

|                                    |       |
|------------------------------------|-------|
| Operating voltage AC max.          | 125 V |
| Operating voltage DC max.          | 125 V |
| Operating voltage AC (UL-listed)   | 30 V  |
| Operating voltage DC (UL-listed)   | 30 V  |
| Current operating per contact max. | 4 A   |

**Installation | Connection**

|              |         |
|--------------|---------|
| Mounting set | M12 x 1 |
|--------------|---------|

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data | Material data**

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

**Cable**

|                                   |                                                                                                                                                        |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Cable identification              | 625                                                                                                                                                    |
| Cable Type                        | 2 (PUR/PVC)                                                                                                                                            |
| Approval (cable)                  | UL (AWM-Style 20549/1731), CSA; CE conform                                                                                                             |
| Cable weight [g/m]                | 54,78 g                                                                                                                                                |
| Material wire                     | Cu wire, bare                                                                                                                                          |
| Resistor (core)                   | max. 57 $\Omega$ /km (20 °C)                                                                                                                           |
| Single wire Ø (core)              | 0.1 mm                                                                                                                                                 |
| Construction (core)               | 42x 0.1 mm (multi-strand wire class 6)                                                                                                                 |
| Diameter (core)                   | 5x 0.34 mm <sup>2</sup>                                                                                                                                |
| AWG                               | similar to AWG 22                                                                                                                                      |
| Material wire isolation           | PVC                                                                                                                                                    |
| Material property wire insulation | CFC-, cadmium-, silicone- and lead-free                                                                                                                |
| Shore hardness wire isolation     | 43 $\pm$ 5 D                                                                                                                                           |
| Wire-Ø incl. isolation            | 1.25 mm $\pm$ 5%                                                                                                                                       |
| Color/numbering of wires          | br, bk, bl, wh, gnye longitudinally striped                                                                                                            |
| Stranding combination             | 5 wires twisted around central filler                                                                                                                  |
| Shield                            | no                                                                                                                                                     |
| Material jacket                   | PUR/PVC                                                                                                                                                |
| Material property (jacket)        | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness jacket             | 80 $\pm$ 5 A (PVC-under jacket); 85 $\pm$ 5 A (PUR-jacket)                                                                                             |
| Outer-Ø (jacket)                  | 5.0 mm $\pm$ 5%                                                                                                                                        |
| Color jacket                      | black                                                                                                                                                  |
| chemical resistance               | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                   | UL 300 V AC                                                                                                                                            |
| Test voltage                      | 2000 V AC                                                                                                                                              |
| Current load capacity             | to DIN VDE 0298-4                                                                                                                                      |

|                                 |                         |
|---------------------------------|-------------------------|
| Temperature range (fixed)       | -30...+80 °C            |
| Temperature range (mobile)      | -5...+80 °C             |
| Bending radius (fixed)          | 10× outer Ø             |
| Bending radius (dynamic)        | 15× outer Ø             |
| No. of bending cycles (C-track) | max. 2 Mio. (25 °C)     |
| Travel speed (C-track)          | max. 3.3 m/s            |
| Acceleration (C-track)          | max. 5 m/s <sup>2</sup> |