

**M12 male 0° / M8 female 90° A-cod. LED**

PUR 3x0.25 bk UL/CSA+drag ch. 8m

Male straight – female 90°





M12 – M8, 3-pole


LED (yellow/green)

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

**Ürün Linki****örnekleme**



Ürün Image farklı olabilir



Cable length 8 m

#### Side 1

|                                           |                   |
|-------------------------------------------|-------------------|
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M12               |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 10 mm             |
| Material contact                          | Copper alloy      |
| Material                                  | PUR               |
| No. of poles                              | 3                 |
| Width across flats                        | SW13              |
| Degree of protection (EN IEC 60529)       | IP66K, IP67       |

#### Side 2

|                                           |                   |
|-------------------------------------------|-------------------|
| Tightening torque                         | 0,4 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M8                |
| Thread                                    | M8 x 1            |
| suitable for corrugated tube (internal Ø) | 6,5 mm            |
| Material contact                          | Copper alloy      |
| Material                                  | PUR               |
| No. of poles                              | 3                 |
| Width across flats                        | SW9               |
| Degree of protection (EN IEC 60529)       | IP66K, IP67       |

#### Ticari bilgiler

|             |          |
|-------------|----------|
| ECLASS-6.0  | 27279218 |
| ECLASS-7.0  | 27061801 |
| ECLASS-8.0  | 27061801 |
| ECLASS-9.0  | 27061801 |
| ECLASS-10.1 | 27060311 |
| ECLASS-11.1 | 27060311 |

|                         |               |
|-------------------------|---------------|
| ECLASS-12.0             | 27060311      |
| ETIM-5.0                | EC001855      |
| GTIN                    | 4048879823166 |
| Gümrük tarife no (gtip) | 85444290      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                                       |      |
|---------------------------------------|------|
| Operating voltage DC                  | 24 V |
| Operating voltage DC min.             | 18 V |
| Operating voltage DC max.             | 30 V |
| Operating voltage DC max. (UL-listed) | 30 V |
| Current operating per contact max.    | 4 A  |
| Current consumption max.              | 5 mA |

**Diagnostics**

|                       |               |
|-----------------------|---------------|
| Status indication LED | green, yellow |
|-----------------------|---------------|

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 0,8 kV            |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data | Material data**

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickeled         |
| Coating of fitting        | nickel plated    |
| Material gasket           | FKM              |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

**Conformity**

|                  |                                                   |
|------------------|---------------------------------------------------|
| Product standard | DIN EN 61076-2-101 (M12), DIN EN 61076-2-114 (M8) |
|------------------|---------------------------------------------------|

**Installation | Cable**

|                                   |                                                                |
|-----------------------------------|----------------------------------------------------------------|
| Cable identification              | 630                                                            |
| Cable Type                        | 3                                                              |
| Jacket Color                      | black                                                          |
| Type of Certificate               | cURus                                                          |
| Amount stranding                  | 1                                                              |
| Stranding                         | 3 wires twisted                                                |
| wire arrangement                  | brown, black, blue                                             |
| No. of bending cycles (C-track)   | 10 Mio. @ 25 °C                                                |
| Cable weight                      | 26,4 g/m                                                       |
| Material jacket                   | PUR                                                            |
| Shore hardness jacket             | 90 ± 5 Shore A                                                 |
| Freedom from ingredients (jacket) | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)           | 4,1 mm                                                         |
| Tolerance outer diameter (sheath) | ± 5 %                                                          |
| Material wire insulation          | PP                                                             |
| Amount wires                      | 3                                                              |
| Outer diameter insulation         | 1,25 mm                                                        |

|                                                         |                                                                |
|---------------------------------------------------------|----------------------------------------------------------------|
| Outer diameter tolerance core insulation                | ± 5 %                                                          |
| Shore hardness wire insulation                          | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                                   | 32                                                             |
| Diameter of single wires                                | 0,1 mm                                                         |
| Conductor crosssection (wire)                           | 0,25 mm²                                                       |
| Material conductor wire                                 | Stranded copper wire, bare                                     |
| Conductor type (wire)                                   | strand class 6                                                 |
| Traversing distance (C-track)                           | 10 m @ 25 °C   horizontal                                      |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                         | 4,5 A                                                          |
| Electrical resistance line constant wire                | 79 Ω/km @ 20 °C                                                |
| Nominal voltage power AC max.                           | 300 V                                                          |
| Power frequency withstand voltage power (wire - jacket) | 2,5 kV @ 60 s                                                  |
| AC withstand voltage power (wire - wire)                | 2,5 kV @ 60 s                                                  |
| Min. operating temperature (static)                     | -40 °C                                                         |
| Max. operating temperature (fixed)                      | 80 °C / 90 °C @ 10000 h Operation                              |
| Operating temperature min. (dynamic)                    | -25 °C                                                         |
| Operating temperature max. (dynamic)                    | 80 °C / 90 °C @ 10000 h Operation                              |
| UV resistance                                           | DIN EN ISO 4892-2 A                                            |
| Flame resistance                                        | UL 1581 § 1090   UL 1581 § 1100 FT2   IEC 60332-2-2            |
| chemical resistance                                     | Good, application-related testing                              |
| Gasoline resistance                                     | Good, application-related testing                              |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (fixed)                                  | 5 x Outer diameter                                             |
| Bending radius (dynamic)                                | 10 x Outer diameter                                            |
| No. of torsion cycles                                   | 2 Mio.                                                         |
| Torsion speed                                           | 35 cycles/min                                                  |
| Torsion stress                                          | ± 180 °/m                                                      |