

## MSUD double valve A-18mm with cable

PUR 4x0.75 bk UL/CSA+drag ch. 30m

Form A (18 mm)

24 V AC  $\pm 20\%$  / DC  $\pm 25\%$

LED and suppression

Connection cable L = 110 mm




Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

## Ürün Linki

### örnekleme



Ürün Image farklı olabilir



Cable length 30 m

### Side 1

Tightening torque 0,4 Nm

|                                                 |                            |
|-------------------------------------------------|----------------------------|
| Thread                                          | M3                         |
| Material                                        | PBT                        |
| <b>Side 2</b>                                   |                            |
| Tightening torque                               | 0,4 Nm                     |
| Thread                                          | M3                         |
| Material                                        | PBT                        |
| <b>Ticari bilgiler</b>                          |                            |
| ECLASS-6.0                                      | 27279218                   |
| ECLASS-6.1                                      | 27279218                   |
| ECLASS-7.0                                      | 27279218                   |
| ECLASS-8.0                                      | 27279218                   |
| ECLASS-9.0                                      | 27060312                   |
| ECLASS-10.1                                     | 27060312                   |
| ECLASS-11.1                                     | 27060312                   |
| ECLASS-12.0                                     | 27060312                   |
| ETIM-5.0                                        | EC001855                   |
| GTIN                                            | 4048879816113              |
| Gümrük tarife no (gtip)                         | 85444290                   |
| Paket miktarı                                   | 1                          |
| <b>Electrical data</b>                          |                            |
| Capacity CX                                     | 20 ms                      |
| <b>Electrical data   Supply</b>                 |                            |
| Operating voltage AC                            | 24 V                       |
| Operating voltage AC min.                       | 19,2 V                     |
| Operating voltage AC max.                       | 28,8 V                     |
| Operating voltage DC                            | 24 V                       |
| Operating voltage DC min.                       | 18 V                       |
| Operating voltage DC max.                       | 30 V                       |
| Cut-off peak voltage max.                       | 55 V                       |
| Current operating per contact max.              | 4 A                        |
| Current consumption max.                        | 12 mA                      |
| <b>Diagnostics</b>                              |                            |
| Status indication LED                           | yellow                     |
| <b>Device protection   Electrical</b>           |                            |
| Degree of protection (EN IEC 60529)             | IP67                       |
| Additional condition protection degree          | inserted, screwed          |
| Pollution Degree                                | 3                          |
| Rated surge voltage                             | 0,8 kV                     |
| Material group (IEC 60664-1)                    | I                          |
| Additional suppressor                           | Diode, Z-Diode             |
| <b>Mechanical data   Material data</b>          |                            |
| Coating locking                                 | verzinkt                   |
| Color housing                                   | black                      |
| Material gasket                                 | PUR                        |
| Locking material                                | Steel                      |
| <b>Mechanical data   Mounting data</b>          |                            |
| Mounting method                                 | inserted, screwed          |
| <b>Environmental characteristics   Climatic</b> |                            |
| Operating temperature min.                      | -25 °C                     |
| Operating temperature max.                      | 85 °C                      |
| Additional condition temperature range          | depending on cable quality |

## Installation | Cable

|                                                         |                                                                |
|---------------------------------------------------------|----------------------------------------------------------------|
| Cable identification                                    | 637                                                            |
| Cable Type                                              | 3                                                              |
| Printing color of wire insulation                       | white (isolation black)                                        |
| Jacket Color                                            | black                                                          |
| Type of Certificate                                     | cURus                                                          |
| Amount stranding                                        | 1                                                              |
| Stranding                                               | 4 wires twisted                                                |
| wire arrangement                                        | black 1, black 2, black 3, green-yellow                        |
| No. of bending cycles (C-track)                         | 10 Mio. @ 25 °C                                                |
| Cable weight                                            | 69,3 g/m                                                       |
| Material jacket                                         | PUR                                                            |
| Shore hardness jacket                                   | 90 ± 5 Shore A                                                 |
| Freedom from ingredients (jacket)                       | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                                 | 6,5 mm                                                         |
| Tolerance outer diameter (sheath)                       | ± 5 %                                                          |
| Material wire insulation                                | PP                                                             |
| Amount wires                                            | 4                                                              |
| Outer diameter insulation                               | 1,85 mm                                                        |
| Outer diameter tolerance core insulation                | ± 5 %                                                          |
| Shore hardness wire insulation                          | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Printing color of wire insulation                       | white (isolation black)                                        |
| Amount strands (wire)                                   | 42                                                             |
| Diameter of single wires                                | 0,15 mm                                                        |
| Conductor crosssection (wire)                           | 0,75 mm²                                                       |
| Material conductor wire                                 | Stranded copper wire, bare                                     |
| Conductor type (wire)                                   | strand class 6                                                 |
| Traversing distance (C-track)                           | 10 m @ 25 °C   horizontal                                      |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                         | 9,6 A                                                          |
| Electrical resistance line constant wire                | 26 Ω/km @ 20 °C                                                |
| Nominal voltage power AC max.                           | 300 V                                                          |
| Power frequency withstand voltage power (wire - jacket) | 2,5 kV @ 60 s                                                  |
| AC withstand voltage power (wire - wire)                | 2,5 kV @ 60 s                                                  |
| Min. operating temperature (static)                     | -40 °C                                                         |
| Max. operating temperature (fixed)                      | 80 °C / 90 °C @ 10000 h Operation                              |
| Operating temperature min. (dynamic)                    | -25 °C                                                         |
| Operating temperature max. (dynamic)                    | 80 °C / 90 °C @ 10000 h Operation                              |
| UV resistance                                           | DIN EN ISO 4892-2 A                                            |
| Flame resistance                                        | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090            |
| chemical resistance                                     | Good, application-related testing                              |
| Gasoline resistance                                     | Good, application-related testing                              |
| Oil resistance                                          | DIN EN 60811-404   Good, application-related testing           |
| Bending radius (fixed)                                  | 5 x Outer diameter                                             |
| Bending radius (dynamic)                                | 10 x Outer diameter                                            |
| No. of torsion cycles                                   | 2 Mio.                                                         |
| Torsion speed                                           | 35 cycles/min                                                  |
| Torsion stress                                          | ± 180 °/m                                                      |