

## MSUD double valve A-18mm with cable

PVC 4x0.75 bk 7.5m

Form A (18 mm)

24 V AC  $\pm 20\%$  / DC  $\pm 25\%$

LED and suppression

Connection cable L = 110 mm



Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

## Ürün Linki

### örnekleme



Ürün Image farklı olabilir



Cable length 7,5 m

### Side 1

Tightening torque 0,4 Nm

|                                                 |                            |
|-------------------------------------------------|----------------------------|
| Thread                                          | M3                         |
| Material                                        | PBT                        |
| <b>Side 2</b>                                   |                            |
| Tightening torque                               | 0,4 Nm                     |
| Thread                                          | M3                         |
| Material                                        | PBT                        |
| <b>Ticari bilgiler</b>                          |                            |
| ECLASS-6.0                                      | 27279218                   |
| ECLASS-6.1                                      | 27279218                   |
| ECLASS-7.0                                      | 27279218                   |
| ECLASS-8.0                                      | 27279218                   |
| ECLASS-9.0                                      | 27060312                   |
| ECLASS-10.1                                     | 27060312                   |
| ECLASS-11.1                                     | 27060312                   |
| ECLASS-12.0                                     | 27060312                   |
| ETIM-5.0                                        | EC001855                   |
| GTIN                                            | 4048879137775              |
| Gümrük tarife no (gtip)                         | 85444290                   |
| Paket miktarı                                   | 1                          |
| <b>Electrical data</b>                          |                            |
| Capacity CX                                     | 20 ms                      |
| <b>Electrical data   Supply</b>                 |                            |
| Operating voltage AC                            | 24 V                       |
| Operating voltage AC min.                       | 19,2 V                     |
| Operating voltage AC max.                       | 28,8 V                     |
| Operating voltage DC                            | 24 V                       |
| Operating voltage DC min.                       | 18 V                       |
| Operating voltage DC max.                       | 30 V                       |
| Cut-off peak voltage max.                       | 55 V                       |
| Current operating per contact max.              | 4 A                        |
| Current consumption max.                        | 12 mA                      |
| <b>Diagnostics</b>                              |                            |
| Status indication LED                           | yellow                     |
| <b>Device protection   Electrical</b>           |                            |
| Degree of protection (EN IEC 60529)             | IP67                       |
| Additional condition protection degree          | inserted, screwed          |
| Pollution Degree                                | 3                          |
| Rated surge voltage                             | 0,8 kV                     |
| Material group (IEC 60664-1)                    | I                          |
| Additional suppressor                           | Diode, Z-Diode             |
| <b>Mechanical data   Material data</b>          |                            |
| Coating locking                                 | verzinkt                   |
| Color housing                                   | black                      |
| Material gasket                                 | PUR                        |
| Locking material                                | Steel                      |
| <b>Mechanical data   Mounting data</b>          |                            |
| Mounting method                                 | inserted, screwed          |
| <b>Environmental characteristics   Climatic</b> |                            |
| Operating temperature min.                      | -25 °C                     |
| Operating temperature max.                      | 85 °C                      |
| Additional condition temperature range          | depending on cable quality |

## Important installation notes

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

## Installation | Cable

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Cable identification                              | 617                                                  |
| Cable Type                                        | 1                                                    |
| Printing color of wire insulation                 | white (isolation black)                              |
| Jacket Color                                      | black                                                |
| Amount stranding                                  | 1                                                    |
| Stranding                                         | 4 wires twisted                                      |
| wire arrangement                                  | black 1, black 2, black 3, green-yellow              |
| Cable weight                                      | 77,66 g/m                                            |
| Material jacket                                   | PVC                                                  |
| Shore hardness jacket                             | 80 ± 5 Shore A                                       |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, silicone-free     |
| Outer-diameter (jacket)                           | 6,5 mm                                               |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                |
| Material wire insulation                          | PVC                                                  |
| Amount wires                                      | 4                                                    |
| Outer diameter insulation                         | 1,8 mm                                               |
| Outer diameter tolerance core insulation          | ± 5 %                                                |
| Shore hardness wire insulation                    | 43 ± 5 Shore D                                       |
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Printing color of wire insulation                 | white (isolation black)                              |
| Amount strands (wire)                             | 24                                                   |
| Diameter of single wires                          | 0,2 mm                                               |
| Conductor crosssection (wire)                     | 0,75 mm²                                             |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | Strand class 5                                       |
| Max. rated voltage (conductor - conductor)        | 500 V                                                |
| Max. rated voltage (conductor - ground)           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 9,6 A                                                |
| Electrical resistance line constant wire          | 26 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 3 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 3 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 70 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| UV resistance                                     | DIN EN ISO 4892-2 A                                  |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1090   UL 1581 § 1100 FT2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |