

**7/8" male 0° with cable**

PUR 5x1.5 gy UL/CSA+drag ch. 3m

Male straight

7/8" (5-pole)





Power cable

with cable sleeves

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**Ürün Linki****örnekleme**

Ürün Image farklı olabilir



Cable length 3 m

**Side 1**

Tightening torque 1,5 Nm

|                          |      |
|--------------------------|------|
| Family construction form | 7/8" |
| Thread                   | 7/8" |
| No. of poles             | 5    |
| Width across flats       | SW22 |

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27279218      |
| ECLASS-6.1              | 27279218      |
| ECLASS-7.0              | 27279218      |
| ECLASS-8.0              | 27279218      |
| ECLASS-9.0              | 27060327      |
| ECLASS-10.1             | 27060311      |
| ECLASS-11.1             | 27060311      |
| ECLASS-12.0             | 27060327      |
| ETIM-5.0                | EC001855      |
| GTIN                    | 4048879399814 |
| Gümrük tarife no (gtip) | 85444290      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                                    |       |
|------------------------------------|-------|
| Current operating per contact max. | 12 A  |
| Current phase - neutral            | 230 V |
| Current phase - phase              | 400 V |

**Installation | Connection**

|                   |        |
|-------------------|--------|
| Tightening torque | 1,5 Nm |
|-------------------|--------|

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP67              |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 3 kV              |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

**Installation | Cable**

|                                   |                                                                                                   |
|-----------------------------------|---------------------------------------------------------------------------------------------------|
| Cable identification              | 961                                                                                               |
| Cable Type                        | 3                                                                                                 |
| Printing color of wire insulation | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black) |
| Jacket Color                      | gray                                                                                              |
| Type of Certificate               | cURus                                                                                             |
| Amount stranding                  | 1                                                                                                 |
| Stranding                         | 5 wires around Filler twisted                                                                     |
| Filler                            | yes                                                                                               |
| wire arrangement                  | green-yellow, blue 2, black 1, white 4, brown 3                                                   |
| Traversing distance (C-track)     | 5 m @ 25 °C                                                                                       |
| Cable weight                      | 129,8 g/m                                                                                         |
| Material jacket                   | PUR                                                                                               |
| Shore hardness jacket             | 90 ± 5 Shore A                                                                                    |
| Freedom from ingredients (jacket) | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                    |
| Outer-diameter (jacket)           | 8 mm                                                                                              |

|                                                   |                                                                                                   |
|---------------------------------------------------|---------------------------------------------------------------------------------------------------|
| Tolerance outer diameter (sheath)                 | ± 5 %                                                                                             |
| Material wire insulation                          | PP                                                                                                |
| Amount wires                                      | 5                                                                                                 |
| Outer diameter insulation                         | 2,3 mm                                                                                            |
| Outer diameter tolerance core insulation          | ± 5 %                                                                                             |
| Shore hardness wire insulation                    | 60 ± 5 Shore D                                                                                    |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                    |
| Printing color of wire insulation                 | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black) |
| Amount strands (wire)                             | 84                                                                                                |
| Diameter of single wires                          | 0,15 mm                                                                                           |
| Conductor crosssection (wire)                     | 1,5 mm <sup>2</sup>                                                                               |
| Material conductor wire                           | Stranded copper wire, bare                                                                        |
| Conductor type (wire)                             | strand class 6                                                                                    |
| Nominal voltage AC max.                           | 1000 V                                                                                            |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                                                                 |
| Current load capacity min. wire                   | 13,5 A                                                                                            |
| Electrical resistance line constant wire          | 13,3 Ω/km @ 20 °C                                                                                 |
| AC withstand voltage (wire - wire)                | 10 kV @ 60 s                                                                                      |
| Power frequency withstand voltage (wire - jacket) | 10 kV @ 60 s                                                                                      |
| Min. operating temperature (static)               | -50 °C                                                                                            |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                                                                 |
| Operating temperature min. (dynamic)              | -25 °C                                                                                            |
| Operating temperature max. (dynamic)              | 80 °C / 90 °C @ 10000 h Operation                                                                 |
| Flame resistance                                  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090                                               |
| chemical resistance                               | Good, application-related testing                                                                 |
| Gasoline resistance                               | Good, application-related testing                                                                 |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing                                              |
| Bending radius (fixed)                            | 7,5 x Outer diameter                                                                              |
| Bending radius (dynamic)                          | 10 x Outer diameter                                                                               |
| Travel speed (C-track)                            | 5 Mio. @ 25 °C                                                                                    |
| No. of torsion cycles                             | 2 Mio.                                                                                            |
| Torsion stress                                    | ± 180 °/m                                                                                         |
| Torsion speed                                     | 35 cycles/min                                                                                     |