

**T-Coupler M8 Nano male / 2x female A-cod.**

4-pol. / 2x 3-pol.

T-coupler (Nano)

Male straight – females straight

M8 – M8, 4-pole



Distribution function (NO)

Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.

**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

|            |          |
|------------|----------|
| ECLASS-6.0 | 27143423 |
| ECLASS-7.0 | 27449001 |
| ECLASS-8.0 | 27449001 |
| ECLASS-9.0 | 27440321 |

|                                                 |                                                                                                                                                       |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| ECLASS-10.1                                     | 27440106                                                                                                                                              |
| ECLASS-11.1                                     | 27440106                                                                                                                                              |
| ECLASS-12.0                                     | 27440106                                                                                                                                              |
| ETIM-5.0                                        | EC002062                                                                                                                                              |
| GTIN                                            | 4048879118491                                                                                                                                         |
| Gümrük tarife no (gtip)                         | 85366990                                                                                                                                              |
| Paket miktarı                                   | 1                                                                                                                                                     |
| <b>Electrical data   Supply</b>                 |                                                                                                                                                       |
| Operating voltage AC max.                       | 32 V                                                                                                                                                  |
| Operating voltage DC max.                       | 32 V                                                                                                                                                  |
| Current operating per contact max.              | 2 A                                                                                                                                                   |
| <b>Installation   Connection</b>                |                                                                                                                                                       |
| Mounting set                                    | M8 x 1                                                                                                                                                |
| <b>Device protection   Electrical</b>           |                                                                                                                                                       |
| Degree of protection (EN IEC 60529)             | IP67                                                                                                                                                  |
| Additional condition protection degree          | inserted, screwed                                                                                                                                     |
| Rated surge voltage                             | 0,8 kV                                                                                                                                                |
| <b>Mechanical data   Mounting data</b>          |                                                                                                                                                       |
| Mounting method                                 | inserted, screwed, Shaking protection                                                                                                                 |
| <b>Environmental characteristics   Climatic</b> |                                                                                                                                                       |
| Operating temperature min.                      | -30 °C                                                                                                                                                |
| Operating temperature max.                      | 80 °C                                                                                                                                                 |
| <b>Important installation notes</b>             |                                                                                                                                                       |
| Note on strain relief                           | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                          | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |