

**Push Pull Power with cable AIDA**

PUR 5x2.5 gy UL/CSA+drag ch. 30m

Male straight

PPP, 5-pole





Push Pull Power

with cable sleeves

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**Ürün Linki****örnekleme**

Ürün Image farklı olabilir

Cable length 30 m

**Ticari bilgiler**

|            |          |
|------------|----------|
| ECLASS-6.0 | 27279218 |
| ECLASS-6.1 | 27279218 |
| ECLASS-7.0 | 27279218 |
| ECLASS-8.0 | 27279218 |
| ECLASS-9.0 | 27060327 |

|                         |               |
|-------------------------|---------------|
| ECLASS-10.1             | 27060311      |
| ECLASS-11.1             | 27060311      |
| ECLASS-12.0             | 27060327      |
| ETIM-5.0                | EC002599      |
| GTIN                    | 4048879871501 |
| Gümrük tarife no (gtip) | 85444290      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 24 V |
| Operating voltage DC max.          | 24 V |
| Current operating per contact max. | 16 A |

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP65, IP67        |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 2                 |

**Mechanical data | Mounting data**

|                    |           |
|--------------------|-----------|
| Looking techniques | Push Pull |
|--------------------|-----------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -40 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

**Installation | Cable**

|                                          |                                                                                                   |
|------------------------------------------|---------------------------------------------------------------------------------------------------|
| Cable identification                     | 962                                                                                               |
| Cable Type                               | 3                                                                                                 |
| Printing color of wire insulation        | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black) |
| Jacket Color                             | gray                                                                                              |
| Type of Certificate                      | cURus                                                                                             |
| Amount stranding                         | 1                                                                                                 |
| Stranding                                | 5 wires around Filler twisted                                                                     |
| Filler                                   | yes                                                                                               |
| wire arrangement                         | green-yellow, blue 2, black 1, white 4, brown 3                                                   |
| Cable weight                             | 190,3 g/m                                                                                         |
| Material jacket                          | PUR                                                                                               |
| Shore hardness jacket                    | 90 ± 5 Shore A                                                                                    |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                    |
| Outer-diameter (jacket)                  | 9,5 mm                                                                                            |
| Tolerance outer diameter (sheath)        | ± 5 %                                                                                             |
| Material wire insulation                 | PP                                                                                                |
| Amount wires                             | 5                                                                                                 |
| Outer diameter insulation                | 2,85 mm                                                                                           |
| Outer diameter tolerance core insulation | ± 5 %                                                                                             |
| Shore hardness wire insulation           | 60 ± 5 Shore D                                                                                    |
| Ingredient freeness wire insulation      | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                    |
| Printing color of wire insulation        | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black) |
| Amount strands (wire)                    | 140                                                                                               |
| Diameter of single wires                 | 0,15 mm                                                                                           |
| Conductor crosssection (wire)            | 2,5 mm²                                                                                           |
| Material conductor wire                  | Stranded copper wire, bare                                                                        |
| Conductor type (wire)                    | strand class 6                                                                                    |
| Traversing distance (C-track)            | 5 m @ 25 °C                                                                                       |
| Nominal voltage AC max.                  | 1000 V                                                                                            |
| Current load capacity (standard)         | to DIN VDE 0298-4                                                                                 |

|                                          |                                                      |
|------------------------------------------|------------------------------------------------------|
| Current load capacity min. wire          | 19,5 A                                               |
| Electrical resistance line constant wire | 8 $\Omega$ /km @ 20 °C                               |
| Min. operating temperature (static)      | -50 °C                                               |
| Max. operating temperature (fixed)       | 80 °C / 90 °C @ 10000 h Operation                    |
| Operating temperature min. (dynamic)     | -25 °C                                               |
| Operating temperature max. (dynamic)     | 80 °C / 90 °C @ 10000 h Operation                    |
| Flame resistance                         | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2  |
| chemical resistance                      | Good, application-related testing                    |
| Gasoline resistance                      | Good, application-related testing                    |
| Oil resistance                           | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (installation)            | x Outer diameter                                     |
| Bending radius (fixed)                   | 7,5 x Outer diameter                                 |
| Bending radius (dynamic)                 | 10 x Outer diameter                                  |
| Travel speed (C-track)                   | 5 Mio. @ 25 °C                                       |
| No. of torsion cycles                    | 2 Mio.                                               |
| Torsion stress                           | $\pm$ 180 °/m                                        |
| Torsion speed                            | 35 cycles/min                                        |