

**M12 Power male 90° L-cod. with cable**

PUR 5x1.5 gy 10m

Power

Male 90°

M12, 5-pole

L-coded

with cable sleeves


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.



Further cable lengths on request.


**Ürün Linki**

örnekleme



|    |      |
|----|------|
| 1  | BN 1 |
| 2  | WH 2 |
| 3  | BU 3 |
| 4  | BK 4 |
| FE | GY 5 |





Ürün Image farklı olabilir



Cable length 10 m

**Side 1**

|                                           |                   |
|-------------------------------------------|-------------------|
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M12P              |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 16,4 mm           |
| Coding                                    | L                 |
| Material contact                          | Copper alloy      |
| No. of poles                              | 5                 |

**Side 2**

Stripping length (jacket) 100 mm

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27279218      |
| ECLASS-6.1              | 27279218      |
| ECLASS-7.0              | 27279218      |
| ECLASS-8.0              | 27279218      |
| ECLASS-9.0              | 27060327      |
| ECLASS-10.1             | 27060311      |
| ECLASS-11.1             | 27060311      |
| ECLASS-12.0             | 27060327      |
| ETIM-5.0                | EC001855      |
| GTIN                    | 4048879742573 |
| Gümrük tarife no (gtip) | 85444290      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage DC max.          | 63 V |
| Current operating per contact max. | 12 A |

**Diagnostics**

|                       |    |
|-----------------------|----|
| Status indication LED | no |
|-----------------------|----|

**Installation | Connection**

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.

Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmalî sınırlıdır. Sürüm: 2024-05-12

Murrelektronik GmbH | Falkenstrasse 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

|                                                 |                                                                                                                           |
|-------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Stripping length (jacket)                       | 100 mm                                                                                                                    |
| Width across flats                              | SW17                                                                                                                      |
| <b>Device protection   Electrical</b>           |                                                                                                                           |
| Degree of protection (EN IEC 60529)             | IP65, IP67                                                                                                                |
| Additional condition protection degree          | inserted, screwed                                                                                                         |
| Pollution Degree                                | 3                                                                                                                         |
| Rated surge voltage                             | 1,5 kV                                                                                                                    |
| Material group (IEC 60664-1)                    | I                                                                                                                         |
| <b>Mechanical data   Material data</b>          |                                                                                                                           |
| Coating locking                                 | Nickeled                                                                                                                  |
| Material housing                                | PUR                                                                                                                       |
| Locking material                                | Zinc die-casting                                                                                                          |
| <b>Mechanical data   Mounting data</b>          |                                                                                                                           |
| Mounting method                                 | inserted, screwed, Shaking protection                                                                                     |
| <b>Environmental characteristics   Climatic</b> |                                                                                                                           |
| Operating temperature min.                      | -25 °C                                                                                                                    |
| Operating temperature max.                      | 85 °C                                                                                                                     |
| Additional condition temperature range          | depending on cable quality                                                                                                |
| <b>Conformity</b>                               |                                                                                                                           |
| Product standard                                | IEC 61076-2-111                                                                                                           |
| <b>Installation   Cable</b>                     |                                                                                                                           |
| Cable identification                            | 966                                                                                                                       |
| Printing color of wire insulation               | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black), white (gray isolation) |
| Printing spacing of wire insulation             | 10 mm                                                                                                                     |
| Jacket Color                                    | gray                                                                                                                      |
| Amount stranding                                | 1                                                                                                                         |
| Stranding                                       | 5 wires around Filler twisted                                                                                             |
| Filler                                          | yes                                                                                                                       |
| wire arrangement                                | gray 5, black 4, blue 3, white 2, brown 1                                                                                 |
| Cable weight                                    | 147,4 g/m                                                                                                                 |
| Material jacket                                 | PUR                                                                                                                       |
| Shore hardness jacket                           | 85 ± 5 Shore A                                                                                                            |
| Freedom from ingredients (jacket)               | lead-free, cadmium-free, CFC-free                                                                                         |
| Outer-diameter (jacket)                         | 8,7 mm                                                                                                                    |
| Tolerance outer diameter (sheath)               | ± 5 %                                                                                                                     |
| Material inner jacket                           | PVC                                                                                                                       |
| Color (inner jacket)                            | gray                                                                                                                      |
| Material wire insulation                        | PVC                                                                                                                       |
| Amount wires                                    | 5                                                                                                                         |
| Outer diameter insulation                       | 2,4 mm                                                                                                                    |
| Outer diameter tolerance core insulation        | ± 5 %                                                                                                                     |
| Shore hardness wire insulation                  | 85 ± 5 Shore A                                                                                                            |
| Ingredient freeness wire insulation             | lead-free, cadmium-free, CFC-free, silicone-free                                                                          |
| Printing color of wire insulation               | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black), white (gray isolation) |
| Printing spacing of wire insulation             | 10 mm                                                                                                                     |
| Amount strands (wire)                           | 30                                                                                                                        |
| Diameter of single wires                        | 0,25 mm                                                                                                                   |
| Conductor crosssection (wire)                   | 1,5 mm <sup>2</sup>                                                                                                       |
| Material conductor wire                         | Stranded copper wire, bare                                                                                                |
| Conductor type (wire)                           | Strand class 5                                                                                                            |
| Nominal voltage AC max.                         | 600 V                                                                                                                     |
| Current load capacity (standard)                | to DIN VDE 0298-4                                                                                                         |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Current load capacity min. wire                   | 13,5 A                                               |
| Electrical resistance line constant wire          | 13,3 $\Omega$ /km @ 20 °C                            |
| AC withstand voltage (wire - wire)                | 4 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 4 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 70 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| Flame resistance                                  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |