

**M12 Power male 0° / female 90° L-cod.**

PUR 5x1.5 bk UL/CSA+drag ch. 1.5m

Power

M12 – M12, 5-pole

Male straight – female 90°

L-coded

with cable sleeves



Plastic housings with good resistance against chemicals and oils.




The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

**Ürün Linki**

örnekleme





Ürün Image farklı olabilir



Cable length 1,5 m

#### Side 1

|                                           |                   |
|-------------------------------------------|-------------------|
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M12P              |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 12 mm             |
| Cable outlet                              | straight          |
| Coding                                    | L                 |
| Material contact                          | Copper alloy      |
| No. of poles                              | 5                 |

#### Side 2

|                          |                   |
|--------------------------|-------------------|
| Tightening torque        | 0,6 Nm            |
| Mounting method          | inserted, screwed |
| Coating contact          | gold plated       |
| Family construction form | M12P              |

|                                                 |                                                                                                                           |
|-------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Thread                                          | M12 x 1                                                                                                                   |
| suitable for corrugated tube (internal Ø)       | 16,4 mm                                                                                                                   |
| Cable outlet                                    | angled                                                                                                                    |
| Coding                                          | L                                                                                                                         |
| Material contact                                | Copper alloy                                                                                                              |
| No. of poles                                    | 5                                                                                                                         |
| <b>Ticari bilgiler</b>                          |                                                                                                                           |
| ECLASS-6.0                                      | 27279218                                                                                                                  |
| ECLASS-6.1                                      | 27279218                                                                                                                  |
| ECLASS-7.0                                      | 27279218                                                                                                                  |
| ECLASS-8.0                                      | 27279218                                                                                                                  |
| ECLASS-9.0                                      | 27060327                                                                                                                  |
| ECLASS-10.1                                     | 27060311                                                                                                                  |
| ECLASS-11.1                                     | 27060311                                                                                                                  |
| ECLASS-12.0                                     | 27060327                                                                                                                  |
| ETIM-5.0                                        | EC001855                                                                                                                  |
| GTIN                                            | 4048879735711                                                                                                             |
| Gümrük tarife no (gtip)                         | 85444290                                                                                                                  |
| Paket miktarı                                   | 1                                                                                                                         |
| <b>Electrical data   Supply</b>                 |                                                                                                                           |
| Operating voltage DC max.                       | 63 V                                                                                                                      |
| Current operating per contact max.              | 12 A                                                                                                                      |
| <b>Diagnostics</b>                              |                                                                                                                           |
| Status indication LED                           | no                                                                                                                        |
| <b>Installation   Connection</b>                |                                                                                                                           |
| Width across flats                              | SW17                                                                                                                      |
| <b>Device protection   Electrical</b>           |                                                                                                                           |
| Degree of protection (EN IEC 60529)             | IP65, IP67                                                                                                                |
| Additional condition protection degree          | inserted, screwed                                                                                                         |
| Pollution Degree                                | 3                                                                                                                         |
| Rated surge voltage                             | 1,5 kV                                                                                                                    |
| Material group (IEC 60664-1)                    | I                                                                                                                         |
| <b>Mechanical data   Material data</b>          |                                                                                                                           |
| Coating locking                                 | Nickeled                                                                                                                  |
| Material gasket                                 | FKM                                                                                                                       |
| Material housing                                | PUR                                                                                                                       |
| Locking material                                | Zinc die-casting                                                                                                          |
| <b>Mechanical data   Mounting data</b>          |                                                                                                                           |
| Mounting method                                 | inserted, screwed, Shaking protection                                                                                     |
| <b>Environmental characteristics   Climatic</b> |                                                                                                                           |
| Operating temperature min.                      | -25 °C                                                                                                                    |
| Operating temperature max.                      | 85 °C                                                                                                                     |
| Additional condition temperature range          | depending on cable quality                                                                                                |
| <b>Conformity</b>                               |                                                                                                                           |
| Product standard                                | IEC 61076-2-111                                                                                                           |
| <b>Installation   Cable</b>                     |                                                                                                                           |
| Cable identification                            | P04                                                                                                                       |
| Cable Type                                      | 3                                                                                                                         |
| Printing color of wire insulation               | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black), white (gray isolation) |
| Jacket Color                                    | black                                                                                                                     |

|                                                         |                                                                                                                           |
|---------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Type of Certificate                                     | cURus                                                                                                                     |
| Amount stranding                                        | 1                                                                                                                         |
| Stranding                                               | 5 wires around Filler twisted                                                                                             |
| Filler                                                  | yes                                                                                                                       |
| wire arrangement                                        | gray 5, black 4, blue 3, white 2, brown 1                                                                                 |
| No. of bending cycles (C-track)                         | 5 Mio. @ 25 °C                                                                                                            |
| Cable weight                                            | 129,8 g/m                                                                                                                 |
| Material jacket                                         | PUR                                                                                                                       |
| Shore hardness jacket                                   | 90 ± 5 Shore A                                                                                                            |
| Freedom from ingredients (jacket)                       | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                                            |
| Outer-diameter (jacket)                                 | 8,2 mm                                                                                                                    |
| Tolerance outer diameter (sheath)                       | ± 5 %                                                                                                                     |
| Material wire insulation                                | PP                                                                                                                        |
| Amount wires                                            | 5                                                                                                                         |
| Outer diameter insulation                               | 2,3 mm                                                                                                                    |
| Outer diameter tolerance core insulation                | ± 5 %                                                                                                                     |
| Shore hardness wire insulation                          | 60 ± 5 Shore D                                                                                                            |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                                            |
| Printing color of wire insulation                       | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black), white (gray isolation) |
| Amount strands (wire)                                   | 84                                                                                                                        |
| Diameter of single wires                                | 0,15 mm                                                                                                                   |
| Conductor crosssection (wire)                           | 1,5 mm <sup>2</sup>                                                                                                       |
| Material conductor wire                                 | Stranded copper wire, bare                                                                                                |
| Conductor type (wire)                                   | strand class 6                                                                                                            |
| Traversing distance (C-track)                           | 5 m @ 25 °C                                                                                                               |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                                                                                         |
| Current load capacity min. wire                         | 13,5 A                                                                                                                    |
| Electrical resistance line constant wire                | 13,3 Ω/km @ 20 °C                                                                                                         |
| Nominal voltage power AC max.                           | 1000 V                                                                                                                    |
| Power frequency withstand voltage power (wire - jacket) | 10 kV @ 60 s                                                                                                              |
| AC withstand voltage power (wire - wire)                | 10 kV @ 60 s                                                                                                              |
| Min. operating temperature (static)                     | -50 °C                                                                                                                    |
| Max. operating temperature (fixed)                      | 80 °C / 90 °C @ 10000 h Operation                                                                                         |
| Operating temperature min. (dynamic)                    | -25 °C                                                                                                                    |
| Operating temperature max. (dynamic)                    | 80 °C / 90 °C @ 10000 h Operation                                                                                         |
| UV resistance                                           | DIN EN ISO 4892-2 A                                                                                                       |
| Flame resistance                                        | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2                                                                       |
| chemical resistance                                     | Good, application-related testing                                                                                         |
| Gasoline resistance                                     | Good, application-related testing                                                                                         |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404                                                                      |
| Bending radius (fixed)                                  | 7,5 x Outer diameter                                                                                                      |
| Bending radius (dynamic)                                | 10 x Outer diameter                                                                                                       |
| No. of torsion cycles                                   | 2 Mio.                                                                                                                    |
| Torsion speed                                           | 35 cycles/min                                                                                                             |
| Torsion stress                                          | ± 180 °/m                                                                                                                 |