

Adapter M12 male/ female B-cod. / D-Sub 9-pol. 35°

Shielded, 12Mbit/s

PROFIBUS

Bus connection plug 35°

SUB-D9 (male); M12× 1 mm, B-coded

Programming device

Ürün Linki

örnekleme



Ürün Image farklı olabilir

Ticari bilgiler

ECLASS-6.0	27061801
ECLASS-7.0	27061801
ECLASS-8.0	27061801
ECLASS-9.0	27061801
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC001855
GTIN	4048879303620
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Electrical data

Terminating resistor connectable, integrated

Electrical data | Supply

Operating voltage DC min.	4,75 V
Operating voltage DC max.	5,25 V
Current consumption max.	12,5 mA

Industrial communication

Data transmission rate max. 12 MBit/s

Installation | Connection

Family construction form M12

Device protection | Electrical

Degree of protection (EN IEC 60529) IP30

Mechanical data | Mounting data

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.

Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmalî sınırlıdır. Sürüm: 2024-05-01

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Height	68 mm
Width	42 mm
Depth	17 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	70 °C

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.