

Female module, 12-pole, crimp t.

250 V (Pin-PE) / 400 V (Pin-Pin), 10 A

Female


12-pole

Crimp

Technical data will be only guaranteed with Murrelektronik components.

Ürün Linki**örnekleme**

Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440217
ECLASS-10.1	27440217
ECLASS-11.1	27440217
ECLASS-12.0	27440217
ETIM-5.0	EC000438
GTIN	4048879641647
Gümrük tarife no (gtip)	85389099
Paket miktarı	5

Electrical data | Supply

Operating voltage AC per power contact max.	400 V
Operating voltage AC per signal contact max.	250 V
Operating voltage DC per power contact max.	400 V
Operating voltage DC per signal contact max.	250 V
Operating current	10 A

Installation

Connection cross section min.	0,14 mm²
-------------------------------	----------

Connection cross section max.	2,5 mm ²
AWG number min.	26
AWG number max.	13
Installation Connection	
Wire insulation diameter min.	3,7 mm
Connection	Crimp
Gender	female
Mating cycles min.	500
Installation Pin assignment	
No. of poles	12
Device protection Electrical	
Pollution Degree	3
Rated surge voltage	4 kV
Insulation resistance min.	100 MΩ
Overvoltage category (EN 60664-1)	II
Overvoltage category (EN 60950-1)	III
Mechanical data	
Holding force contacts min.	70 N
Holding force modules min.	150 N
Pulling force max.	60 N
Mechanical data Material data	
Coating contact	versilbert, vergoldet
Combustibility class (UL94)	V-0
Material housing	PA
Material contact	Brass
Mechanical data Mounting data	
Number of module slots	1
Height	43,5 mm
Width	14,5 mm
Depth	34,4 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	125 °C
Climatic category (EN IEC 60068-1)	40/125/10