



## PRE-WIRED CAP FOR EXACT8, 8XM8, 4-POL

5.0m PUR/PVC 16x0,34+2x0,75

PUR/PVC  
5.0 m

### Ürün Linki

örnekleme



Ürün Image farklı olabilir



### Ticari bilgiler

|             |          |
|-------------|----------|
| ECLASS-6.0  | 27143423 |
| ECLASS-6.1  | 27279219 |
| ECLASS-7.0  | 27279219 |
| ECLASS-8.0  | 27279219 |
| ECLASS-9.0  | 27440108 |
| ECLASS-10.1 | 27440108 |
| ECLASS-11.1 | 27440108 |
| ECLASS-12.0 | 27440108 |

|                                                  |                                                                                                                                                                        |
|--------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ETIM-5.0                                         | EC002585                                                                                                                                                               |
| GTIN                                             | 4048879298469                                                                                                                                                          |
| Gümrük tarife no (gtip)                          | 85444290                                                                                                                                                               |
| Paket miktarı                                    | 1                                                                                                                                                                      |
| <b>Electrical data   Supply</b>                  |                                                                                                                                                                        |
| Total current max.                               | 8 A                                                                                                                                                                    |
| <b>Device protection   Media</b>                 |                                                                                                                                                                        |
| Flame resistance                                 | flame retardant                                                                                                                                                        |
| <b>Mechanical data   Material data</b>           |                                                                                                                                                                        |
| Material housing                                 | Plastic                                                                                                                                                                |
| <b>Environmental characteristics   Climatic</b>  |                                                                                                                                                                        |
| Operating temperature min.                       | -20 °C                                                                                                                                                                 |
| Operating temperature max.                       | 80 °C                                                                                                                                                                  |
| Additional condition temperature range           | depending on cable quality                                                                                                                                             |
| <b>Installation   Cable</b>                      |                                                                                                                                                                        |
| STOOW style jacket                               | Hybrid, Signal, Power                                                                                                                                                  |
| Cable identification                             | 395                                                                                                                                                                    |
| Cable Type                                       | 2                                                                                                                                                                      |
| Jacket Color                                     | gray                                                                                                                                                                   |
| Type of Certificate                              | cURus                                                                                                                                                                  |
| Amount stranding                                 | 1                                                                                                                                                                      |
| Stranding                                        | 6 wires around Core filler twisted                                                                                                                                     |
| Amount stranding (type 2)                        | 1                                                                                                                                                                      |
| Stranding (type 2)                               | 12 wires around Stranding combination twisted                                                                                                                          |
| wire arrangement                                 | black, violet, gray-pink, red-blue, green-white, brown-green, (brown-gray, gray-white, brown-yellow, yellow-white, red, pink, gray, yellow, green, white, brown, blue) |
| Cable weight                                     | 154 g/m                                                                                                                                                                |
| Material jacket                                  | PUR                                                                                                                                                                    |
| Shore hardness jacket                            | 87 ± 5 Shore A                                                                                                                                                         |
| Freedom from ingredients (jacket)                | lead-free, cadmium-free, CFC-free, silicone-free                                                                                                                       |
| Outer-diameter (jacket)                          | 9,6 mm                                                                                                                                                                 |
| Tolerance outer diameter (sheath)                | ± 5 %                                                                                                                                                                  |
| Material inner jacket                            | PVC                                                                                                                                                                    |
| Color (inner jacket)                             | gray                                                                                                                                                                   |
| Material wire insulation                         | PVC                                                                                                                                                                    |
| Amount wires                                     | 16                                                                                                                                                                     |
| Outer diameter insulation                        | 1,3 mm                                                                                                                                                                 |
| Outer diameter tolerance core insulation         | ± 5 %                                                                                                                                                                  |
| Shore hardness wire insulation                   | 43 ± 5 Shore D                                                                                                                                                         |
| Material properties wire insulation              | good machinability                                                                                                                                                     |
| Ingredient freeness wire insulation              | lead-free, cadmium-free, CFC-free, silicone-free                                                                                                                       |
| Amount strands (wire)                            | 19                                                                                                                                                                     |
| Diameter of single wires                         | 0,15 mm                                                                                                                                                                |
| Conductor crosssection (wire)                    | 0,34 mm²                                                                                                                                                               |
| Material conductor wire                          | Stranded copper wire, bare                                                                                                                                             |
| Conductor type (wire)                            | Strand class 5                                                                                                                                                         |
| Traversing distance (C-track)                    | 5 m @ 25 °C                                                                                                                                                            |
| Travel speed (C-track)                           | 2                                                                                                                                                                      |
| Material wire insulation (Power)                 | PVC                                                                                                                                                                    |
| Outer diameter wire insulation (Power)           | 1,8 mm                                                                                                                                                                 |
| Tolerance outer diameter wire insulation (Power) | ±5 %                                                                                                                                                                   |
| Shore hardness wire insulation (Power)           | 43±5 Shore D                                                                                                                                                           |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Material properties wire insulation (Power)       | good machinability                                   |
| Ingredient freeness wire insulation (Power)       | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands wire (Power)                       | 42                                                   |
| Diameter of single wires (Power)                  | 0,15 mm                                              |
| Wire conductor cross section (Power)              | 0,75 mm²                                             |
| Material conductor wire (Power)                   | Stranded copper wire, bare                           |
| Conductor type wire (Power)                       | strand class 6                                       |
| Max. rated voltage (conductor - conductor)        | 300 V                                                |
| Max. rated voltage (conductor - ground)           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4 A                                                  |
| Loop resistance                                   | 7,8 A                                                |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                      |
| Electrical resistance coating wire (Power)        | 26 Ω/km @20 °C                                       |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| Flame resistance                                  | UL 1581 § 1090   UL 1581 § 1100 FT2   IEC 60332-2-2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |
| Travel speed (C-track)                            | 2 Mio. @ 25 °C                                       |

#### Connection type 2

|                          |                |
|--------------------------|----------------|
| Family construction form | free cable end |
| No. of poles             | 10             |
| Family construction form | M8             |
| Gender                   | female         |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 4              |
| PIN 1                    | +              |
| PIN 2                    | S 2            |
| PIN 3                    | -              |
| PIN 4                    | S 1            |