

## EXACT12, 8XM12, 4 POLE MOULDED CABLE

10.0m PUR 8x0,34+3X0.75

8-way, 4-pole

PUR/PVC

without LED, up to 125 V AC/DC

10.0 m



Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.

### Ürün Linki

örnekleme



Ürün Image farklı olabilir



### Ticari bilgiler

|            |          |
|------------|----------|
| ECLASS-6.0 | 27143423 |
| ECLASS-6.1 | 27279219 |
| ECLASS-7.0 | 27279219 |

|                                                 |                                                                                   |
|-------------------------------------------------|-----------------------------------------------------------------------------------|
| ECLASS-8.0                                      | 27279219                                                                          |
| ECLASS-9.0                                      | 27440108                                                                          |
| ECLASS-10.1                                     | 27440108                                                                          |
| ECLASS-11.1                                     | 27440108                                                                          |
| ECLASS-12.0                                     | 27440108                                                                          |
| ETIM-5.0                                        | EC002585                                                                          |
| GTIN                                            | 4048879054201                                                                     |
| Gümrük tarife no (gtip)                         | 85444290                                                                          |
| Paket miktarı                                   | 1                                                                                 |
| <b>Electrical data   Supply</b>                 |                                                                                   |
| Operating voltage AC                            | 125 V                                                                             |
| Operating voltage DC                            | 125 V                                                                             |
| Current operating per contact max.              | 4 A                                                                               |
| <b>Installation   Connection</b>                |                                                                                   |
| Mounting set                                    | M12 x 1                                                                           |
| <b>Device protection   Electrical</b>           |                                                                                   |
| Degree of protection (EN IEC 60529)             | IP65, IP67                                                                        |
| <b>Device protection   Media</b>                |                                                                                   |
| Flame resistance                                | flame retardant                                                                   |
| <b>Mechanical data   Material data</b>          |                                                                                   |
| Material housing                                | Plastic                                                                           |
| <b>Mechanical data   Mounting data</b>          |                                                                                   |
| Mounting method                                 | Schraubgewinde                                                                    |
| <b>Environmental characteristics   Climatic</b> |                                                                                   |
| Operating temperature min.                      | -20 °C                                                                            |
| Operating temperature max.                      | 70 °C                                                                             |
| Additional condition temperature range          | depending on cable quality                                                        |
| <b>Installation   Cable</b>                     |                                                                                   |
| STOOW style jacket                              | Hybrid, Signal, Power                                                             |
| Cable identification                            | 362                                                                               |
| Cable Type                                      | 2                                                                                 |
| Jacket Color                                    | gray                                                                              |
| Type of Certificate                             | cURus                                                                             |
| Amount stranding                                | 1                                                                                 |
| Stranding                                       | 2 wires with Filler twisted                                                       |
| Amount stranding (type 2)                       | 1                                                                                 |
| Stranding (type 2)                              | 9 wires around Stranding combination twisted                                      |
| Filler                                          | yes                                                                               |
| wire arrangement                                | white, violet, (green, yellow, gray, pink, red, black, brown, blue, green-yellow) |
| Cable weight                                    | 115,5 g/m                                                                         |
| Material jacket                                 | PUR                                                                               |
| Shore hardness jacket                           | 87 ± 5 Shore A                                                                    |
| Freedom from ingredients (jacket)               | lead-free, cadmium-free, CFC-free, silicone-free                                  |
| Outer-diameter (jacket)                         | 8,1 mm                                                                            |
| Tolerance outer diameter (sheath)               | ± 5 %                                                                             |
| Material inner jacket                           | PVC                                                                               |
| Color (inner jacket)                            | gray                                                                              |
| Material wire insulation                        | PVC                                                                               |
| Amount wires                                    | 8                                                                                 |
| Outer diameter insulation                       | 1,3 mm                                                                            |
| Outer diameter tolerance core insulation        | ± 5 %                                                                             |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Shore hardness wire insulation                    | 43 ± 5 Shore D                                       |
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands (wire)                             | 19                                                   |
| Diameter of single wires                          | 0,15 mm                                              |
| Conductor crosssection (wire)                     | 0,34 mm <sup>2</sup>                                 |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | Strand class 5                                       |
| Traversing distance (C-track)                     | 5 m @ 25 °C                                          |
| Travel speed (C-track)                            | 3                                                    |
| Material wire insulation (Power)                  | PVC                                                  |
| Outer diameter wire insulation (Power)            | 1,8 mm                                               |
| Tolerance outer diameter wire insulation (Power)  | ±5 %                                                 |
| Shore hardness wire insulation (Power)            | 43±5 Shore D                                         |
| Material properties wire insulation (Power)       | good machinability                                   |
| Ingredient freeness wire insulation (Power)       | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands wire (Power)                       | 24                                                   |
| Diameter of single wires (Power)                  | 0,2 mm                                               |
| Wire conductor cross section (Power)              | 0,75 mm <sup>2</sup>                                 |
| Material conductor wire (Power)                   | Stranded copper wire, bare                           |
| Conductor type wire (Power)                       | Strand class 5                                       |
| Max. rated voltage (conductor - conductor)        | 300 V                                                |
| Max. rated voltage (conductor - ground)           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4 A                                                  |
| Loop resistance                                   | 7,8 A                                                |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                      |
| Electrical resistance coating wire (Power)        | 26 Ω/km @20 °C                                       |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| Flame resistance                                  | UL 1581 § 1090   IEC 60332-2-2   UL 1581 § 1100 FT2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |
| Travel speed (C-track)                            | 2 Mio. @ 25 °C                                       |

#### Connection type 2

|                          |                |
|--------------------------|----------------|
| Family construction form | free cable end |
| No. of poles             | 11             |
| Family construction form | M12            |
| Gender                   | female         |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 4              |
| PIN 1                    | +              |
| PIN 2                    | n.c.           |
| PIN 3                    | -              |

|       |        |
|-------|--------|
| PIN 4 | NO S 1 |
| PIN 5 | PE     |