

M12 male 0° L-cod. field- wireable (IDC)

5-pol. 0.75...1.5mm² 5.8-13.5mm

Customized printing and packaging

Male straight

M12, 5-pole

IDC terminals




Sealing range (cable Ø)

5.8...13.5 mm

The resistance to aggressive media should be individually tested for your application. Further details on request.

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Side 1

Family construction form	M12P
Coding	L
No. of poles	5

Ticari bilgiler

ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-8.0	27440102
ECLASS-9.0	27440116
ECLASS-10.1	27440102
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ETIM-5.0	EC001855
GTIN	4048879849456
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Electrical data | Supply

Operating voltage DC max.	63 V
Current operating per contact max.	12 A

Diagnostics

Status indication LED	no
-----------------------	----

Installation

Connection cross section min.	0,75 mm ²
Connection cross section max.	1,5 mm ²

Installation | Connection

Tightening torque	0,6 Nm
Mounting set	M12 x 1
Width across flats	SW17

Device protection | Electrical

Material group (IEC 60664-1)	III
------------------------------	-----

Mechanical data | Material data

Coating contact	gold plated
Coating of fitting	nickel plated
Material contact carrier	PA
Material screw connection	Zinc die-casting

Mechanical data | Mounting data

Mounting method	inserted, screwed, Shaking protection
Clamping range min.	5,8 mm
Clamping range max.	13,5 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	85 °C

Conformity

Product standard	DIN EN 61076-2-101 (M12)
------------------	--------------------------