

**M8 male 0° / M8 female 0°**

TPE 4x22AWG ye UL/CSA, ITC/PLTC 7,5m

USA

Male straight – female straight



M8 – M8, 4-pole

without cable sleeves


Further cable lengths on request.


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.


**Ürün Linki****örnekleme**

|   |    |   |
|---|----|---|
| 1 | BN | 1 |
| 2 | WH | 2 |
| 3 | BU | 3 |
| 4 | BK | 4 |





Ürün Image farklı olabilir



Cable length 7,5 m

**Side 1**

Tightening torque 0,4 Nm

Mounting method inserted, screwed

Family construction form M8

Thread M8 x 1

suitable for corrugated tube (internal Ø) 10 mm

No. of poles 4

Width across flats SW9

**Side 2**

Tightening torque 0,4 Nm

Mounting method inserted, screwed

Family construction form M8

Thread M8 x 1

No. of poles 4

**Ticari bilgiler**

ECLASS-6.0 27279218

ECLASS-6.1 27279218

ECLASS-7.0 27279218

ECLASS-8.0 27279218

ECLASS-9.0 27060311

ECLASS-10.1 27060311

ECLASS-11.1 27060311

ECLASS-12.0 27060311

ETIM-5.0 EC001855

GTIN 4048879759250

Gümrük tarife no (gtip) 85444290

Paket miktarı 1

**Electrical data | Supply**

Operating voltage AC max. 50 V

Operating voltage DC max. 60 V

Operating voltage AC (UL-listed) 30 V

|                                                 |                                                                                                                                                       |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating voltage DC (UL-listed)                | 30 V                                                                                                                                                  |
| Current operating per contact max.              | 4 A                                                                                                                                                   |
| <b>Diagnostics</b>                              |                                                                                                                                                       |
| Status indication LED                           | no                                                                                                                                                    |
| <b>Device protection   Electrical</b>           |                                                                                                                                                       |
| Degree of protection (EN IEC 60529)             | IP65, IP67, IP68, IP66K                                                                                                                               |
| Additional condition protection degree          | inserted, screwed                                                                                                                                     |
| Pollution Degree                                | 3                                                                                                                                                     |
| Rated surge voltage                             | 1,5 kV                                                                                                                                                |
| Material group (IEC 60664-1)                    | I                                                                                                                                                     |
| <b>Mechanical data   Material data</b>          |                                                                                                                                                       |
| Coating locking nut                             | nickel plated                                                                                                                                         |
| Locking screw coating                           | nickel plated                                                                                                                                         |
| Material housing                                | PUR                                                                                                                                                   |
| Locking nut material                            | Zinc die-casting                                                                                                                                      |
| Locking material screw                          | Brass                                                                                                                                                 |
| <b>Mechanical data   Mounting data</b>          |                                                                                                                                                       |
| Mounting method                                 | inserted, screwed, Shaking protection                                                                                                                 |
| <b>Environmental characteristics   Climatic</b> |                                                                                                                                                       |
| Operating temperature min.                      | -25 °C                                                                                                                                                |
| Operating temperature max.                      | 85 °C                                                                                                                                                 |
| Additional condition temperature range          | depending on cable quality                                                                                                                            |
| <b>Important installation notes</b>             |                                                                                                                                                       |
| Note on strain relief                           | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                          | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| <b>Conformity</b>                               |                                                                                                                                                       |
| Product standard                                | DIN EN 61076-2-114 (M8)                                                                                                                               |
| <b>Installation   Cable</b>                     |                                                                                                                                                       |
| Cable identification                            | U04                                                                                                                                                   |
| Jacket Color                                    | yellow                                                                                                                                                |
| Type of Certificate                             | cURus                                                                                                                                                 |
| Amount stranding                                | 1                                                                                                                                                     |
| Stranding                                       | 4 wires twisted                                                                                                                                       |
| wire arrangement                                | brown, black, blue, white                                                                                                                             |
| Cable weight                                    | 49,5 g/m                                                                                                                                              |
| Material jacket                                 | TPE                                                                                                                                                   |
| Freedom from ingredients (jacket)               | lead-free, CFC-free, halogen-free                                                                                                                     |
| Outer-diameter (jacket)                         | 5,36 mm                                                                                                                                               |
| Tolerance outer diameter (sheath)               | ± 5 %                                                                                                                                                 |
| Material wire insulation                        | PVC                                                                                                                                                   |
| Amount wires                                    | 4                                                                                                                                                     |
| Outer diameter insulation                       | 1,27 mm                                                                                                                                               |
| Outer diameter tolerance core insulation        | ± 5 %                                                                                                                                                 |
| Ingredient freeness wire insulation             | lead-free, CFC-free                                                                                                                                   |
| Amount strands (wire)                           | 19                                                                                                                                                    |
| Diameter of single wires                        | 22 AWG                                                                                                                                                |
| Conductor crosssection (wire)                   | 22 AWG                                                                                                                                                |
| Material conductor wire                         | Stranded copper wire, bare                                                                                                                            |
| Nominal voltage AC max.                         | 300 V                                                                                                                                                 |
| Current load capacity (standard)                | to DIN VDE 0298-4                                                                                                                                     |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Current load capacity min. wire                   | 4,8 A                                                |
| Electrical resistance line constant wire          | 46,9 $\Omega$ /km @ 20 °C                            |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -40 °C                                               |
| Max. operating temperature (fixed)                | 105 °C                                               |
| Operating temperature min. (dynamic)              | -20 °C                                               |
| Operating temperature max. (dynamic)              | 90 °C                                                |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |
| Travel speed (C-track)                            | 10 Mio.                                              |
| No. of torsion cycles                             | 3 Mio.                                               |
| Torsion stress                                    | $\pm 180$ °/m                                        |