

Product discontinued until 31.10.2018, replaced by: 56471

Gateway Profibus-DP/AS-i, 1 Master, Spec. 3.0, IP20

Gateway-Singlemaster

via pluggable spring clamp plug-in terminals on the front 0.5...1.5 mm²

AS-Interface/PROFIBUS DP

Specification 3.0

Current manuals, GSD/type data can be downloaded at: www.murrelektronik.com


Other gateways on request.

Link to Product

Illustration



Product may differ from Image



取引条件

ECLASS-6.0	27242208
ECLASS-7.0	27242208
ECLASS-8.0	27242208
ECLASS-9.0	27242208
ETIM-5.0	EC001604
GTIN	4048879495684
HSコード	85176200
Packaging unit	1

Electrical data

Rated operating current AS-Interface max.	200 mA
---	--------

Electrical data | Supply

Operating voltage DC	30 V
----------------------	------

Industrial communication | Bus data

Address range default setting	3
Address range min.	1
Address range max.	126
Address setting type	Buttons, PROFIBUS
Automatic baudrate detection	yes

このデータシートに含まれる情報は最大限の注意を払って作成されました。

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-22

Murrelektronik GmbH | Falkenstr. 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Baud rate min.	9,6 kBaud
Baud rate max.	12 MBaud
Industrial communication AS-Interface	
AS-i specification	V3.0
Number of slaves max.	62
Diagnostic interface serial	RJ45/Ethernet
Cycle time AS-i	150 µs × (number of slaves + 2)
Installation Connection	
Family construction form	SUB-D9
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	500 V
Mechanical data	
Number of operating buttons	4
Function operating buttons	ESC, Mode, OK, Set
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	120 mm
Width	85 mm
Depth	83 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Conformity	
Low Voltage Directive	EN 50295