

Gateway CC-Link/AS-i, 1 Master, P24

Spec. 3.0, Power 24


AS-Interface/CC-Link
Power 24V
Specification 3.0
Current manuals, GSD/type data can be downloaded at: www.murrelektronik.com
Other gateways on request.
Gateway-Singlemaster
AS-Interface data decoupling integrated
AS-Interface duplicate address detection
AS-Interface EMC detector integrated

Link to Product

Illustration



Product may differ from Image



取引条件		
ECLASS-6.0		27242608
ECLASS-6.1		27242608
ECLASS-7.0		27242608
ECLASS-8.0		27242608
ECLASS-9.0		27242608
ECLASS-10.1		27242608
ECLASS-11.1		27242608
ECLASS-12.0		27242608
ETIM-5.0		EC001604
GTIN		4048879661683
HSコード		85176200
Packaging unit		1
Electrical data		
Rated operating current AS-Interface max.		250 mA
Security level		PELV
Electrical data Supply		

Operating voltage DC	24 V
Operating voltage DC min.	20 V
Operating voltage DC max.	30,6 V

Industrial communication

Supported protocol	CC-Link
--------------------	---------

Industrial communication | Bus data

Automatic baudrate detection	no
Baud rate min.	156 kBaud
Baud rate max.	10 MBaud

Industrial communication | AS-Interface

AS-i specification	V3.0
Number of slaves max.	62
Diagnostic interface serial	None
Cycle time AS-i	150 µs × (number of slaves + 2)

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	500 V

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	120 mm
Width	85 mm
Depth	83 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C

Conformity

Product standard	EN 61131-2, EN 62026-2
------------------	------------------------