

CUBE20S DIGITAL OUTPUT MODULE DO2

2x24VDC 0,5A NPN

Expansion module
Digital outputs
DO2 - (E) NPN

[Link to Product](#)

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ETIM-5.0	EC001599
GTIN	4048879424295
HSコード	85389099
Packaging unit	1
Electrical data Supply	
Norm operating voltage	EN 61131-2
Operating voltage UA DC	24 V
Current consumption max.	60 mA
Total current UA max.	1 A
module supply	via system connection
Electrical data Output	
Actuator current UA per output max.	0,5 A
Overload resistant	yes
Short-circuit protected	yes
Type Output	NPN (EN 61131-2)
Output current per pin max.	0,5 A
Output delay time	175 ns

Lamp load 5 W

Diagnostics

Diagnostic	Under voltage
Diagnostic via BUS	per module
Diagnostic via LED	per module and channel
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Galvanic separation (operating voltage)	yes
Galvanic separation output/output	yes

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	109 mm
Width	12,9 mm
Depth	76,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	70 °C

Connection type 2

Connection type 1	Power
Connection type 2	Power
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	DO 0
PIN 2	24 V DC
PIN 3	0 V
PIN 5	DO 1
PIN 6	24 V DC
PIN 7	0 V