

Emergency stop with 2 positive opening

contacts in a IP65 enclosure

E-Stop / R-B 42 2NC 1NO M12(8)

with M12 connection

8-pole

Emergency-Stop button

2 NC (positively-opening)

1 button (1 NO contact)

Delivery contents:




Flat lens, transparent clear, red, yellow, green, blue

Label plates, O, I, R

mounting with clip on the back side

[Link to Product](#)

Illustration



Product may differ from Image



取引条件

ECLASS-6.0

27371244

このデータシートに含まれる情報は最大限の注意を払って作成されました。

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-07

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ECLASS-6.1	27371244
ECLASS-7.0	27371244
ECLASS-8.0	27371244
ECLASS-9.0	27371244
ECLASS-10.1	27371244
ECLASS-11.1	27371244
ECLASS-12.0	27371244
ETIM-5.0	EC002034
GTIN	4048879594264
HSコード	85365080
Packaging unit	1
Electrical data Supply	
Operating voltage DC min.	1 V
Operating voltage DC max.	36 V
Operating voltage DC (UL-listed)	30 V
Operating current	1,5 A
Device protection	
Condition lifetime	load-dependent, temperature dependent
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	50000 Cycles
Device protection Mechanical	
Mechanical endurance	50000 Cycles
Operating life B10d	250000 Cycles
Mechanical data	
Bounce time max.	10 ms
Mechanical data Material data	
Material contact	AgNi
Mechanical data Mounting data	
Height	52 mm
Width	124 mm
Depth	42 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Technical Data Reliability	
Lambda normally closed contact	20 %
Connection type 1	
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	8
PIN 1	NC 1
PIN 2	NC 1 +
PIN 3	NC 2
PIN 4	NC 2 +

PIN 5	NO
PIN 6	NO