

Mico Pro PS 10-100-240/24

IN: 90- 265VAC OUT: 24-28V/10ADC

INPUT: 90...265 V AC

OUTPUT: 24...28 V DC

Current: 10 A

Build your own Mico Pro® online:


[START](#)

Mains failure bridging min.

min. 44 ms (115 V AC); min. 44 ms (230 V AC)

Ürün Linki
örnekleme


Ürün Image farklı olabilir


Ticari bilgiler

ECLASS-6.0	27141901
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC001440
GTIN	4048879695817
Gümrük tarife no (gtip)	85044083
Paket miktarı	1

Electrical data

Number of devices parallel connection max.	2
Parallel connection	yes
Series connection	no

Security level SELV

Electrical data | Supply

Power frequency 50 ... 60 Hz

Electrical data | Input

Fuse protection primary side internal 6,3 A

CTRL input voltage control inputs high min. 9 V

CTRL input voltage control inputs high max. 30 V

CTRL signal ON/OFF

Characteristic back-up fuse Inertia

Input voltage 1 AC 115 V

Input voltage 2 AC 230 V

Input voltage AC min. 90 V

Input voltage AC max. 265 V

Input current at input voltage 1 AC 3,7 A

Input current at input voltage 2 AC 1,7 A

Inrush current max. 25 A

ON input voltage control inputs min. 9 V

ON input voltage control inputs max. 30 V

ON pulse length control inputs high min. 120 ms

Efficiency 91,8 % @ 115 V AC, 93,6 % @ 230 V AC

Electrical data | Output

Output voltage DC 24 V

Output voltage DC min. 24 V

Output voltage DC max. 28 V

Output voltage adjustable yes

Output current 10 A

Ripple effective max. 20 mV

Switching voltage AC max. 30 V

Switching voltage DC max. 30 V

Spikes (s-s) max. 380 mV

Installation | Connection

Connection Push-In spring clamp terminals

Device protection | Electrical

Degree of protection (EN IEC 60529) IP20

Overload protection output yes

Short-circuit protection output yes

Overtemperature protection output yes

Mechanical data | Mounting data

Mounting method geschnappt

Suitable for mounting type Mounting rail TH35, (EN 60715)

Height 130 mm

Width 74 mm

Depth 114 mm

Environmental characteristics | Climatic

Operating temperature min. -25 °C

Operating temperature max. 55 °C

Storage temperature min. -40 °C

Storage temperature max. 85 °C

Relative humidity min. (operation) 5 %

Relative humidity max. (operation) 95 % no condensation

Conformity

Product standard	IEC 61010-2-201
EMC	EN 61000-3-2