

CUBE20S ANALOG INPUT MODULE AI2

2X16Bit TH 22 Parameter Bytes


Expansion module
AI2 - (E) TC
for thermo elements

Link to Product

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27242601
ECLASS-6.1	27242601
ECLASS-7.0	27242601
ECLASS-8.0	27242601
ECLASS-9.0	27242601
ECLASS-10.1	27242601
ECLASS-11.1	27242601
ECLASS-12.0	27242601
ETIM-5.0	EC001596
GTIN	4048879423496
HSコード	85389099
Packaging unit	1
Electrical data Supply	
Idle current external max.	30 mA
Current consumption max.	75 mA
module supply	via system connection
Electrical data Input	
Type input	E, B, C, J, K, L, N, R, S, T
Conversion time analog input per channel max.	324,1 ms
Diagnostics	
Diagnostic	Under voltage

Diagnostic via BUS	per module
Diagnostic via LED	per module and channel
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	109 mm
Width	12,9 mm
Depth	76,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-20 °C
Storage temperature max.	85 °C

Connection type 2

Connection type 1	Power
Connection type 2	Power
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	+ TC 0
PIN 2	- TC 0
PIN 5	+ TC 1
PIN 6	- TC 1