

MVP12 plastic DI16 IOL HUB

IO-Link Version 1.1


Compact module
IO-Link V1.1
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link to Product

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
GTIN	4048879695688
HSコード	85369010
Packaging unit	1
Electrical data Input	
Type input	PNP (EN 61131-2) Type 3
Input filter time	1 ms
Industrial communication IO-Link	
IO-Link type	Device
Port Class	A
IO-Link revision ID	V1.1
IO-Link transmission rate	COM2 (38.4 kbit/s)

IO-Link cycle time min. 2,3 ms

Diagnostics	
Diagnostic via LED	per module and channel
IO-Link events	No voltage, Undervoltage supply
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67

Mechanical data Mounting data	
Suitable for mounting type	2-hole screw mounting
Height	126 mm
Width	50 mm
Depth	34,5 mm

Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	70 °C

Connection type 4	
Connection type 1	X0-X7
Connection type 2	X0-X7
Connection type 3	XZ1
Connection type 4	XZ1
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	24 V DC (US)
PIN 2	DI
PIN 3	0 V
PIN 4	DI
PIN 5	n.c.
Family construction form	M12
Gender	female
Coding	A
No. of poles	5
PIN 1	24 V DC US
PIN 2	DI
PIN 3	0 V
PIN 4	DI
PIN 5	n.c.
Family construction form	M12
Gender	male
Coding	A
No. of poles	5
PIN 1	24 V DC US
PIN 2	n.c.
PIN 3	0 V
PIN 4	IO-Link
PIN 5	n.c.

Family construction form	M12
Gender	male
Coding	A
No. of poles	5
PIN 1	24 V DC (US)
PIN 2	n.c.
PIN 3	0 V
PIN 4	IO-Link
PIN 5	n.c.