




MSDD-AU7AB 1LED DIREKTANSCHL.F.M.-VENTIL

24 V AC/DC $\pm 25\%$
LED and suppressor diode
4-pole
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

取引条件	
ECLASS-6.0	27143423
ECLASS-7.0	27449001
ECLASS-8.0	27449001
ECLASS-9.0	27440321
ETIM-5.0	EC001855
GTIN	4048879238052
HSコード	85366990
Packaging unit	50
Electrical data Supply	
Operating voltage AC	24 V
Operating voltage AC min.	18 V

Operating voltage AC max.	30 V
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Current operating per contact max.	4 A
Diagnostics	
Status indication LED	yellow
Installation Connection	
Tightening torque	0,6 Nm
Mounting set	M12 x 1
Installation Pin assignment	
No. of poles	2 + PE
Device protection Electrical	
Additional suppressor	Suppressor diode
Mechanical data Mounting data	
Mounting method	inserted, screwed
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Important installation notes	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.