



M12 male 90° A-cod. screw terminal

5-pol., max. 0,75mm², 4 - 6mm


Male 90°  
M12, 5-pole  
Screw terminals  
Sealing range (cable Ø): 4...6 mm  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image



| Side 1                   |                   |
|--------------------------|-------------------|
| Tightening torque        | 0,6 Nm            |
| Mounting method          | inserted, screwed |
| Family construction form | M12               |
| Thread                   | M12 x 1           |

|                                     |      |
|-------------------------------------|------|
| Gender                              | male |
| Coding                              | A    |
| No. of poles                        | 5    |
| Width across flats                  | SW18 |
| Degree of protection (EN IEC 60529) | IP67 |

Side 2

|                 |                |
|-----------------|----------------|
| Mounting method | field-wireable |
|-----------------|----------------|

取引条件

|                |               |
|----------------|---------------|
| ECLASS-6.0     | 27279221      |
| ECLASS-7.0     | 27440104      |
| ECLASS-8.0     | 27440104      |
| ECLASS-9.0     | 27440102      |
| ECLASS-10.1    | 27440102      |
| ECLASS-11.1    | 27440102      |
| ECLASS-12.0    | 27440116      |
| ETIM-5.0       | EC002635      |
| GTIN           | 4048879201599 |
| HSコード          | 85366990      |
| Packaging unit | 1             |

Electrical data | Supply

|                                           |       |
|-------------------------------------------|-------|
| Operating voltage AC max.                 | 60 V  |
| Operating voltage DC max.                 | 60 V  |
| Operating voltage AC max. (UL-listed)     | 125 V |
| Operating voltage DC max. (UL-listed)     | 125 V |
| Current operating per contact max.        | 4 A   |
| Current operating per contact max. (URc.) | 3 A   |

Diagnostics

|                       |    |
|-----------------------|----|
| Status indication LED | no |
|-----------------------|----|

Installation

|                               |                           |
|-------------------------------|---------------------------|
| Connection cross section max. | 0,75 mm²                  |
| Rotation option               | 90° (4 outlet directions) |

Installation | Connection

|                    |        |
|--------------------|--------|
| Tightening torque  | 0,6 Nm |
| Width across flats | SW18   |

Device protection

|          |    |
|----------|----|
| Shielded | no |
|----------|----|

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Overvoltage category (EN 60664-1)      | III               |
| Overvoltage category (EN 60950-1)      | II                |

Mechanical data | Material data

|                  |    |
|------------------|----|
| Material housing | PA |
|------------------|----|

Mechanical data | Mounting data

|                     |                                       |
|---------------------|---------------------------------------|
| Mounting method     | inserted, screwed, Shaking protection |
| Clamping range min. | 4 mm                                  |
| Clamping range max. | 6 mm                                  |
| Height              | 41 mm                                 |
| Width               | 40 mm                                 |

Depth 20 mm

Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -40 °C |
| Operating temperature max. | 85 °C  |

Important installation notes

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |