



M12 female recept. A-cod. shielded rear

PUR 5x0.34 shielded bk UL/CSA+drag ch. 2m


Flange female  
M12, 5-pole  
shielded  
Rear mounting  
Further cable lengths on request.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image



|                   |        |
|-------------------|--------|
| Cable length      | 2 m    |
| Side 1            |        |
| Tightening torque | 0,6 Nm |

|                                     |                   |
|-------------------------------------|-------------------|
| Mounting method                     | inserted, screwed |
| Coating contact                     | gold plated       |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Coding                              | A                 |
| Material contact                    | Copper alloy      |
| Material                            | Brass             |
| No. of poles                        | 5                 |
| Degree of protection (EN IEC 60529) | IP67              |

Side 2

|                           |             |
|---------------------------|-------------|
| Stripping length (jacket) | 20 mm       |
| Coating contact           | gold plated |

取引条件

|                |               |
|----------------|---------------|
| ECLASS-6.0     | 27279220      |
| ECLASS-6.1     | 27279220      |
| ECLASS-7.0     | 27440103      |
| ECLASS-8.0     | 27440103      |
| ECLASS-9.0     | 27440103      |
| ECLASS-10.1    | 27440103      |
| ECLASS-11.1    | 27440103      |
| ECLASS-12.0    | 27440103      |
| ETIM-5.0       | EC001855      |
| GTIN           | 4048879529457 |
| HSコード          | 85444290      |
| Packaging unit | 1             |

Electrical data | Supply

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 60 V |
| Operating voltage DC max.          | 60 V |
| Current operating per contact max. | 4 A  |

Diagnostics

|                       |    |
|-----------------------|----|
| Status indication LED | no |
|-----------------------|----|

Installation | Connection

|                           |           |
|---------------------------|-----------|
| Stripping length (jacket) | 20 mm     |
| Mounting set              | M16 x 1.5 |
| Width across flats        | SW19      |

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Protection NEMA                        | 3, 4, 6P          |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

Mechanical data | Material data

|                           |               |
|---------------------------|---------------|
| Coating locking           | nickel plated |
| Coating of fitting        | nickel plated |
| Material gasket           | FKM           |
| Locking material          | Brass         |
| Material screw connection | Brass         |

Mechanical data | Mounting data

|                    |                |
|--------------------|----------------|
| Mounting method    | Schraubgewinde |
| Looking techniques | Schraubgewinde |

Environmental characteristics | Climatic

|                                                   |                                                                                                                                                       |
|---------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating temperature min.                        | -25 °C                                                                                                                                                |
| Operating temperature max.                        | 85 °C                                                                                                                                                 |
| Additional condition temperature range            | depending on cable quality                                                                                                                            |
| Important installation notes                      |                                                                                                                                                       |
| Note on strain relief                             | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                            | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Approvals                                         |                                                                                                                                                       |
| UL 50E                                            | yes                                                                                                                                                   |
| Installation   Cable                              |                                                                                                                                                       |
| Cable identification                              | 642                                                                                                                                                   |
| Cable Type                                        | 3                                                                                                                                                     |
| Jacket Color                                      | black                                                                                                                                                 |
| Type of Certificate                               | cURus                                                                                                                                                 |
| Amount stranding                                  | 1                                                                                                                                                     |
| Stranding                                         | 5 wires around Core filler twisted                                                                                                                    |
| Cable shielding (type)                            | copper braid, tinned                                                                                                                                  |
| Cable shielding (coverage)                        | 80 %                                                                                                                                                  |
| Banding                                           | Fleece, Foil                                                                                                                                          |
| Filler                                            | yes                                                                                                                                                   |
| wire arrangement                                  | brown, black, blue, white, green-yellow                                                                                                               |
| Cable weighth                                     | 57,2 g/m                                                                                                                                              |
| Material jacket                                   | PUR                                                                                                                                                   |
| Shore hardness jacket                             | 90 ± 5 Shore A                                                                                                                                        |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                                                                        |
| Outer-diameter (jacket)                           | 5,6 mm                                                                                                                                                |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                                                                                                                 |
| Material wire insulation                          | PP                                                                                                                                                    |
| Amount wires                                      | 5                                                                                                                                                     |
| Outer diameter insulation                         | 1,25 mm                                                                                                                                               |
| Outer diameter tolerance core insulation          | ± 5 %                                                                                                                                                 |
| Shore hardness wire insulation                    | 70 ± 5 Shore D                                                                                                                                        |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                                                                        |
| Amount strands (wire)                             | 42                                                                                                                                                    |
| Diameter of single wires                          | 0,1 mm                                                                                                                                                |
| Conductor crossection (wire)                      | 0,34 mm²                                                                                                                                              |
| Material conductor wire                           | Stranded copper wire, bare                                                                                                                            |
| Conductor type (wire)                             | strand class 6                                                                                                                                        |
| Traversing distance (C-track)                     | 5 m @ 25 °C   horizontal                                                                                                                              |
| Nominal voltage AC max.                           | 300 V                                                                                                                                                 |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                                                                                                                     |
| Current load capacity min. wire                   | 4,5 A                                                                                                                                                 |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                                                                                                                       |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                                                                                                                           |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                                                                                                                           |
| AC withstand voltage (wire - shield)              | 2 kV @ 60 s                                                                                                                                           |
| Min. operating temperature (static)               | -40 °C                                                                                                                                                |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                                                                                                                     |
| Operating temperature min. (dynamic)              | -25 °C                                                                                                                                                |
| Operating temperature max. (dynamic)              | 80 °C / 90 °C @ 10000 h Operation                                                                                                                     |
| UV resistance                                     | DIN EN ISO 4892-2 A                                                                                                                                   |
| Flame resistance                                  | UL 1581 § 1090   IEC 60332-2-2   UL 1581 § 1100 FT2                                                                                                   |

|                          |                                                      |
|--------------------------|------------------------------------------------------|
| chemical resistance      | Good, application-related testing                    |
| Gasoline resistance      | Good, application-related testing                    |
| Oil resistance           | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)   | 5 x Outer diameter                                   |
| Bending radius (dynamic) | 10 x Outer diameter                                  |
| Travel speed (C-track)   | 5 Mio. @ 25 °C                                       |
| No. of torsion cycles    | 2 Mio.                                               |
| Torsion stress           | ± 30 °/m                                             |
| Torsion speed            | 35 cycles/min                                        |